

Eaton's Arrow Hart  
EZ Link™ modular devices

# EZ Link modular devices

Increase productivity  
and labor-savings on your  
next commercial project.

## Fast to the finish

# Arrow Hart



**EATON**

*Powering Business Worldwide*



# Big job? Make it EZ!

Arrow Hart EZ Link™ modular devices are the most efficient way to wire receptacles and switches for large commercial projects.

**Save time and money** with EZ Link modular devices!



## Standard & Decorator Receptacles

Standard & tamper resistant duplex & decorator receptacles [pg. 4](#)



## Controlled Receptacles

Half controlled & dual controlled duplex & decorator receptacles [pg. 5](#)



## Split Circuit Receptacles

Split circuit duplex & decorator receptacles [pg. 6](#)



## Slim GFCI Receptacles

Standard & tamper resistant GFCIs [pg. 7](#)



## Hospital Grade Receptacles

Standard & tamper resistant hospital grade duplex & decorator receptacles [pg. 8](#)



## Toggle & Decorator Switches

Toggle & decorator switches [pg. 9](#)



## EZ Link Connectors

Receptacle & switch connectors [pg. 10](#)




# The EZ Link Advantage

Designed with contractors in mind to help meet deadlines while saving on labor costs, our EZ Link devices feature a unique design for quick and easy installation – faster than traditional wiring.

Engineered from the ground up, the revolutionary design reduces installation errors and allows for secure, aligned and accurate installation the first time... every time.

## Revolutionary Design

The EZ Link's thoughtful design allows for efficient, accurate and dependable installation.




### Features & Benefits


- 1. Sliding Installation**  
Unique sliding design allows the connector to simply slide into place faster and easier.
- 2. Guide Rails**  
Provide accurate and secure alignment during installation.
- 3. Arrow Design**  
The design easily identifies the direction to slide in the connector, providing safety against incorrect installation.
- 4. Release Wings**  
Wings provide an easy, one-hand release of the device, while providing two points of capture for connection retention.
- 5. Easy Labeling**  
A dedicated labeling area adds convenience for special labeling needs.
- 6. Wire Relief Slots**  
Allow sharp bending to make it easier to push all the wires back into the box during final installation.
- 7. Gripping Ridges**  
Tactile design incorporated into the connector provides a secure grip for the installers.

## Slim Profile

EZ Link devices occupy less space in the electrical box compared to standard receptacles. Connectors feature wire relief slots which enable wires to be bent at angle exceeding 90 degrees, making it easier to positing the device within the electrical box.



Traditional Wiring



EZ Link Wiring



Scan QR code to access our EZ Link video.



Scan QR code to access additional EZ Link resources.



# Heavy-duty duplex & decorator receptacles

## FEATURES

- Intuitive arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- Connectors slide and lock into place on back of device, guided by precision rails and custom engineered wings resulting in unmatched connector retention
- Discrete connector designs prevent incorrect installations

## APPLICATIONS

Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link receptacles have been designed to meet the requirements of commercial and industrial applications, while speeding up installation with a simple and convenient sliding termination type design. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.

## DESCRIPTION

**2-pole, 3-wire grounding**  
**15A, 125V/AC**  
**20A, 125V/AC**



5-15R

5-20R

## DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

A	Rating V/AC	NEMA	Description	Catalog no.	Color suffix
15	125	5-15R	<b>Duplex</b>	<input type="checkbox"/> <b>EZ5262</b> __	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> <b>EZ5362</b> __	B, BK, GY, LA, RD, V, W
15	125	5-15R	<b>Decorator duplex</b>	<input type="checkbox"/> <b>EZ6262</b> __	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> <b>EZ6362</b> __	B, BK, GY, LA, RD, V, W

## TAMPER RESISTANT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

A	Rating V/AC	NEMA	Description	Catalog no.	Color suffix
15	125	5-15R	<b>Tamper resistant duplex</b>	<input type="checkbox"/> <b>EZTR5262</b> __	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> <b>EZTR5362</b> __	B, BK, GY, LA, RD, V, W
15	125	5-15R	<b>Tamper resistant decorator duplex</b>	<input type="checkbox"/> <b>EZTR6262</b> __	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> <b>EZTR6362</b> __	B, BK, GY, LA, RD, V, W

## SPECIFICATIONS

### Electrical

**Dielectric voltage:** Withstands 2000V per UL 498  
**Current interrupting:** Yes, at full-rated current  
**Temperature rise:** Max. 30°C (86°F) after Fed Spec Current Overload Test Procedure  
**Frequency:** 60 Hz; Voltage: 125V  
**Amperage:** 15A/20A  
**Maximum interrupting capacity:** 20 Amps

### Testing & code compliance

cULus Listed to UL 498, file no. E15058  
 Meets all UL 498, Fed Spec W-C-596 testing standards, applicable CSA requirements and NOM certified

### Environmental

**Flammability:** Meets UL 94 requirements; V2 rated  
**Temperature rating:** -20°C to 60°C (-4°F to 140°F)

### Mechanical

**Terminal accommodation:** With separable terminals use connectors EZRCSTR or EZRCSOL  
**Voltage ratings:** Permanently marked on device



EZ5262W



EZTR5262W

## AVAILABLE IN THESE COLORS

\*For ordering devices, include Cat. no. followed by the color suffix, for example: EZTR5262\_\_

<b>B</b>	<b>BK</b>	<b>GY</b>	<b>LA</b>	<b>RD</b>	<b>V</b>	<b>W</b>
Brown	Black	Gray	Light Almond	Red	Ivory	White

## MATERIALS

<b>Housing</b>	Top: 8202 Nylon Bottom: 8202 Nylon
<b>Strap</b>	0.047" Thick galvanized steel
<b>Line contacts</b>	0.032" Thick brass C260
<b>Terminal</b>	0.032" Thick brass C260





# Heavy-duty half & dual controlled receptacles

## FEATURES

- Intuitive arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- Offered in both dual and half controlled option for ease of use for one outlet or both
- Connectors slide and lock into place on back of device, guided by precision rails and custom engineered wings resulting in unmatched connector retention
- Discrete connector designs prevent incorrect installations
- Tamper resistant receptacles comply with 2023 NEC Article 406.12

## APPLICATIONS


Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link half controlled and dual controlled receptacles have been designed to meet energy conservation code requirements for commercial projects, while speeding up installation with a simple and convenient sliding termination type design. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.

## DESCRIPTION

**2-pole, 3-wire grounding**  
**15A, 125V/AC**  
**20A, 125V/AC**

FCU/S

NOM



5-15R 5-20R

## HALF CONTROLLED DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

A	Rating		Description	Catalog no.	Color suffix
	V/AC	NEMA			
15	125	5-15R	Duplex	<input type="checkbox"/> EZ5262CH	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ5362CH	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	Decorator duplex	<input type="checkbox"/> EZ6262CH	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ6362CH	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	Tamper resistant duplex	<input type="checkbox"/> EZTR5262CH	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR5362CH	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	Tamper resistant decorator duplex	<input type="checkbox"/> EZTR6262CH	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR6362CH	B, BK, GN, GY, LA, RD, V, W

## DUAL CONTROLLED DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

A	Rating		Description	Catalog no.	Color suffix
	V/AC	NEMA			
15	125	5-15R	Duplex	<input type="checkbox"/> EZ5262CD	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ5362CD	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	Decorator duplex	<input type="checkbox"/> EZ6262CD	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ6362CD	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	Tamper resistant duplex	<input type="checkbox"/> EZTR5262CD	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR5362CD	B, BK, GN, GY, LA, RD, V, W
15	125	5-15R	Tamper resistant decorator duplex	<input type="checkbox"/> EZTR6262CD	B, BK, GN, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR6362CD	B, BK, GN, GY, LA, RD, V, W

## SPECIFICATIONS

### Electrical

**Dielectric voltage:** Withstands 2000V per UL 498  
**Current interrupting:** Yes, at full-rated current  
**Temperature rise:** Max. 30°C (86°F) after Fed Spec Current Overload Test Procedure  
**Frequency:** 60 Hz; Voltage: 125V  
**Amperage:** 15A/20A  
**Maximum interrupting capacity:** 20 Amps

### Testing & code compliance


cULus Listed to UL 498, file no. E15058  
 Meets all UL 498, Fed Spec W-C-596 testing standards, applicable CSA requirements and NOM certified

### Environmental

**Flammability:** Meets UL 94 requirements; V2 rated  
**Temperature rating:** -20°C to 60°C (-4°F to 140°F)

### Mechanical

**Terminal accommodation :** With separable terminals use connectors EZRCSTR or EZRC SOL  
**Voltage ratings:** Permanently marked on device



## AVAILABLE IN THESE COLORS

\*For ordering devices, include Cat. no. followed by the color suffix, for example: EZTR5362CD\_

B	BK	GN	GY	LA	RD	V	W
Brown	Black	Green	Gray	Light Almond	Red	Ivory	White

## MATERIALS

<b>Housing</b>	Top: 8202 Nylon Bottom: 8202 Nylon
<b>Strap</b>	0.047" Thick steel, galvanized
<b>Line contacts</b>	0.032" Thick brass C260
<b>Terminal</b>	0.032" Thick brass C260



# Heavy-duty split circuit receptacles

## FEATURES

- Intuitive Arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- Split circuit allows for control of one outlet through an attached traveler wire
- Connectors slide and lock into place on back of device, guided by precision rails and custom engineered wings resulting in unmatched connector retention
- Discrete connector designs prevent incorrect installations
- Tamper resistant receptacles comply with 2023 NEC Article 406.12

## APPLICATIONS

Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link standard receptacles have been designed to meet the requirements of commercial and industrial applications, while speeding up installation with a simple and convenient sliding termination type design. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.

## DESCRIPTION

2-pole, 3-wire grounding  
15A, 125V/AC  
20A, 125V/AC



## SPLIT CIRCUIT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

A	Rating		Description	Catalog no.	Color suffix
	V/AC	NEMA			
15	125	5-15R	Duplex	<input type="checkbox"/> EZ5262SC	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ5362SC	B, BK, GY, LA, RD, V, W
15	125	5-15R	Decorator duplex	<input type="checkbox"/> EZ6262SC	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ6362SC	B, BK, GY, LA, RD, V, W

## SPLIT CIRCUIT TAMPER RESISTANT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

A	Rating		Description	Catalog no.	Color suffix
	V/AC	NEMA			
15	125	5-15R	Tamper resistant duplex	<input type="checkbox"/> EZTR5262SC	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR5362SC	B, BK, GY, LA, RD, V, W
15	125	5-15R	Tamper resistant decorator duplex	<input type="checkbox"/> EZTR6262SC	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR6362SC	B, BK, GY, LA, RD, V, W

## SPECIFICATIONS

### Electrical

**Dielectric voltage:** Withstands 2000V per UL 498  
**Current interrupting:** Yes, at full-rated current  
**Temperature rise:** Max. 30°C (86°F) after Fed Spec Current Overload Test Procedure  
**Frequency:** 60 Hz; Voltage: 125V  
**Amperage:** 15A/20A  
**Maximum interrupting capacity:** 20 Amps

### Testing & code compliance


cULus Listed to UL 498 and file no. E15058  
 UL 498 (receptacles), applicable CSA requirements and NOM certified

### Environmental

**Flammability:** Meets UL 94 requirements; V2 rated  
**Temperature rating:** -20°C to 60°C (-4°F to 140°F)

### Mechanical

**Terminal accommodation:** With separable terminals use connectors EZRCSTR or EZRCSOL  
**Voltage ratings:** Permanently marked on device



## AVAILABLE IN THESE COLORS

\*For ordering devices, include Cat. no. followed by the color suffix, for example: EZTR5262SC\_

<b>B</b>	<b>BK</b>	<b>GY</b>	<b>LA</b>	<b>RD</b>	<b>V</b>	<b>W</b>
Brown	Black	Gray	Light Almond	Red	Ivory	White

## MATERIALS

<b>Housing</b>	Top: 8202 Nylon Bottom: 8202 Nylon
<b>Strap</b>	0.047" Thick galvanized steel
<b>Line contacts</b>	0.032" Thick brass C260
<b>Terminal</b>	0.032" Thick brass C260



# Slim GFCI receptacles

## FEATURES

- Intuitive arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- Connectors slide and lock into place on back of device, guided by precision rails and custom engineered wings resulting in unmatched connector retention
- Discrete connector designs prevent incorrect installations
- Wider button wells for easy TEST and RESET
- Intuitive LED status indicators for trip and end of life states
- Aesthetic design with reduced top housing markings and neutral text direction on buttons
- Automatically self-tests periodically to ensure GFCI protection
- Tamper resistant receptacles comply with 2023 NEC Article 406.12

## APPLICATIONS

Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link GFCI receptacles have been designed to meet the requirements of commercial and industrial applications, while speeding up installation with a simple and convenient sliding termination type. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.



EZGF20W

EZTRGF15W

## AVAILABLE IN THESE COLORS

\*For ordering devices, include Cat. no. followed by the color suffix, for example: EZTRGF15\_


<b>B</b>	<b>BK</b>	<b>GY</b>	<b>LA</b>	<b>RD</b>	<b>V</b>	<b>W</b>
Brown	Black	Gray	Light Almond	Red	Ivory	White

## MATERIALS

<b>Housing</b>	Top: Thermoplastic, polycarbonate Bottom: 8202 Nylon
<b>Strap</b>	0.047" Thick steel, zinc-plated
<b>Line contacts</b>	0.030" Copper alloy
<b>Terminal</b>	0.030" Copper alloy

## DESCRIPTION

2-pole, 3-wire grounding  
15A, 125V/AC  
20A, 125V/AC



## SLIM GFCI RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating	A	V/AC	NEMA	Description	Catalog no.	Color suffix
15	125	5-15R	SLIM GFCI		<input type="checkbox"/> EZGF15_	B, BK, GY, LA, RD, V, W
20	125	5-20R			<input type="checkbox"/> EZGF20_*	B, BK, GY, LA, RD, V, W

## SLIM TAMPER RESISTANT GFCI RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating	A	V/AC	NEMA	Description	Catalog no.	Color suffix
15	125	5-15R	SLIM TAMPER RESISTANT GFCI		<input type="checkbox"/> EZTRGF15_	B, BK, GY, LA, RD, V, W
20	125	5-20R			<input type="checkbox"/> EZTRGF20_*	B, BK, GY, LA, RD, V, W

\*FedSpec certification on 20A only

## SPECIFICATIONS

<b>Electrical</b>	<p><b>Dielectric voltage:</b> Withstands 2000V per UL 498</p> <p><b>Current interrupting:</b> Yes, at full-rated current</p> <p><b>Temperature rise:</b> Max. 30°C (86°F) after Fed Spec Current Overload Test Procedure</p> <p><b>Frequency:</b> 60 Hz</p> <p><b>Voltage:</b> 125V</p> <p><b>Amperage:</b> 15A/20A</p> <p><b>Maximum interrupting capacity:</b> 20 Amps</p> <p><b>Short circuit testing:</b> Meets and exceeds 2KA</p> <p><b>Trip time:</b> 0.025 seconds (Class A)</p>
<b>Testing &amp; code compliance</b>	<p>cULus Listed to UL 498 and UL 943, file no. E60120</p> <p>Meets all UL 943 (GFCI), UL 498 (receptacles) and applicable CSA requirements; NOM certified; Federal Specification W-C-596H for 20A models</p>
<b>Environmental</b>	<p><b>Flammability:</b> Meets UL 94 requirements; V2 rated</p> <p><b>Temperature rating:</b> -35C to 66C (-31F to 150F)</p>
<b>Mechanical</b>	<p><b>Terminal accommodation:</b> With separable terminals use connectors EZRCSTR or EZRCOL</p> <p><b>Voltage ratings:</b> Permanently marked on device</p>





# Hospital grade receptacles

## FEATURES


- Intuitive arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- Child-safety black tamper resistant shutters help prevent improper insertion of foreign objects
- Connectors slide and lock into place on back of device, guided by precision rails and custom engineered wings resulting in unmatched connector retention
- Discrete connector designs prevent incorrect installations
- Complies with 2023 NEC Article 406.12

## APPLICATIONS

Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link tamper resistant Hospital Grade receptacles have been designed to meet the requirements of healthcare applications, while speeding up installation with a simple and convenient sliding termination type design. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.

## DESCRIPTION

**2-pole, 3-wire grounding**  
**15A, 125V/AC**  
**20A, 125V/AC**



## DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		NEMA	Description	Catalog no.	Color suffix
A	V/AC				
15	125	5-15R	Duplex	<input type="checkbox"/> EZ8200__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ8300__	B, BK, GY, LA, RD, V, W
15	125	5-15R	Decorator duplex	<input type="checkbox"/> EZ8262__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZ8362__	B, BK, GY, LA, RD, V, W

## TAMPER RESISTANT DUPLEX RECEPTACLES, SEPARABLE TERMINAL TYPE

Rating		NEMA	Description	Catalog no.	Color suffix
A	V/AC				
15	125	5-15R	Tamper resistant duplex	<input type="checkbox"/> EZTR8200__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR8300__	B, BK, GY, LA, RD, V, W
15	125	5-15R	Tamper resistant decorator duplex	<input type="checkbox"/> EZTR8262__	B, BK, GY, LA, RD, V, W
20	125	5-20R		<input type="checkbox"/> EZTR8362__	B, BK, GY, LA, RD, V, W

## SPECIFICATIONS

### Electrical

**Dielectric voltage:** Withstands 2000V per UL 498  
**Current interrupting:** Yes, at full-rated current  
**Temperature rise:** Max. 30°C (86°F) after Fed Spec Current Overload Test Procedure  
**Frequency:** 60 Hz; Voltage: 125V  
**Amperage:** 15A/20A  
**Maximum interrupting capacity:** 20 Amps

### Testing & code compliance

cULus Listed to UL 498, file no. E15058  
 Meets all UL 498, Fed Spec W-C-596 testing standards, applicable CSA requirements and NOM certified

### Environmental

**Flammability:** Meets UL 94 requirements; V2 rated  
**Temperature rating:** -20°C to 60°C (-4°F to 140°F)

### Mechanical

**Terminal accommodation:** With separable terminals use connectors EZRCSTR or EZRCSOL  
**Voltage ratings:** Permanently marked on device



## AVAILABLE IN THESE COLORS

\*For ordering devices, include Cat. no. followed by the color suffix, for example: EZTR8300\_\_

<b>B</b>	<b>BK</b>	<b>GY</b>	<b>LA</b>	<b>RD</b>	<b>V</b>	<b>W</b>
Brown	Black	Gray	Light Almond	Red	Ivory	White

## MATERIALS

<b>Housing</b>	Top: 8202 Nylon Bottom: 8202 Nylon
<b>Strap</b>	0.047" Galvanized steel
<b>Line contacts</b>	0.032" Thick brass C260
<b>Terminal</b>	0.032" Thick brass C260





# Heavy-duty single pole & 3-way switches

## FEATURES


- Intuitive arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- 120/277V/AC rating ideal for fluorescent lighting fixtures typical in commercial applications
- Color-coded faces identify amperage: blue=15 amp, red=20 amp
- Connectors slide and lock into place on back of device, guided by precision rails and custom engineered wings resulting in unmatched connector retention
- Discrete connector designs prevent incorrect installations

## APPLICATIONS

Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link single pole and 3-way switches have been designed to meet the requirements of commercial and industrial applications, while speeding up installation with a simple and convenient sliding termination type design. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.

## DESCRIPTION

**Single pole, 3-way**  
**15A & 20A, 120/277 V/AC**



### TOGGLE SWITCHES, SEPARABLE TERMINAL TYPE


A	Rating V/AC	Description	Catalog no.	Color suffix
15	120/277	<b>Single pole toggle</b>	<input type="checkbox"/> <b>EZ1201</b> __	B, BK, GY, LA, RD, V, W
20			<input type="checkbox"/> <b>EZ1221</b> __	B, BK, GY, LA, RD, V, W
15	120/277	<b>3-way toggle</b>	<input type="checkbox"/> <b>EZ1203</b> __	B, BK, GY, LA, RD, V, W
20			<input type="checkbox"/> <b>EZ1223</b> __	B, BK, GY, LA, RD, V, W

### DECORATOR SWITCHES, SEPARABLE TERMINAL TYPE

A	Rating V/AC	Description	Catalog no.	Color suffix
15	120/277	<b>Single pole decorator</b>	<input type="checkbox"/> <b>EZ7601</b> __	B, BK, GY, LA, RD, V, W
20			<input type="checkbox"/> <b>EZ7621</b> __	B, BK, GY, LA, RD, V, W
15	120/277	<b>3-way decorator</b>	<input type="checkbox"/> <b>EZ7603</b> __	B, BK, GY, LA, RD, V, W
20			<input type="checkbox"/> <b>EZ7623</b> __	B, BK, GY, LA, RD, V, W

## SPECIFICATIONS

<b>Electrical</b>	<b>Dielectric voltage:</b> Withstands 2000V per UL 498 <b>Temperature rise:</b> Max. 30°C (86°F) after 100 cycles of overload @ 150% of rated current (DC) <b>Frequency:</b> 60 Hz; Voltage: 120/277V/AC <b>Amperage:</b> 15A/20A
<b>Testing &amp; code compliance</b>	cULus Listed to UL 20, file no. E18704 Meets all UL20 (switches), applicable CSA requirements and NOM certified
<b>Environmental</b>	<b>Flammability:</b> Meets UL 94 requirements; V2 rated <b>Temperature rating:</b> -20°C to 60°C (-4°F to 140°F)
<b>Mechanical</b>	<b>Terminal accommodation:</b> With separable terminals use connectors EZSPSWSTR, EZSPWSOL, EZ3WSWSTR, EZ3WSWSOL <b>Voltage ratings:</b> Permanently marked on device



EZ1203W

EZ7603W

## AVAILABLE IN THESE COLORS

\*For ordering devices, include Cat. no. followed by the color suffix, for example: EZ7603\_\_

<b>B</b>	<b>BK</b>	<b>GY</b>	<b>LA</b>	<b>RD</b>	<b>V</b>	<b>W</b>
Brown	Black	Gray	Light Almond	Red	Ivory	White

## MATERIALS

<b>Housing</b>	Top: Thermoplastic, polycarbonate Bottom: 8202 Nylon
<b>Strap</b>	0.047" Galvanized steel
<b>Line contacts</b>	0.032" Thick brass C260
<b>Terminal</b>	0.032" Thick brass C260



# EZ Link switch & receptacle connectors

## FEATURES

- Intuitive arrow-shaped mating design and slim profile allows for rapid installation during trim-out
- Discrete connector designs prevent incorrect installations
- Connector wire relief shapes allow sharp wire bending to provide wire location flexibility within the wallbox
- Flexible release arms allow an easy one-hand release operation while providing two points of capture to stay attached to device

## APPLICATIONS

Leveraging Arrow Hart's existing feature-rich and high quality products, EZ Link connectors have been designed to meet the requirements of commercial and industrial applications, while speeding up installation with a simple and convenient sliding design. EZ Link fulfills a need for customers who want to reduce project timelines through quick installation of wiring devices.

## DESCRIPTION

**2-pole, 3-wire receptacle connector**  
20A, 125V/AC



**Single pole, 3-wire switch connector**  
**3-way, 4-wire switch connector**  
20A, 120/277VAC

## RECEPTACLE & SWITCH CONNECTORS


Description	Wire Type	Catalog no.	Color
Receptacle connector	Stranded	<input type="checkbox"/> EZRCSTR	Blue
Receptacle connector	Solid	<input type="checkbox"/> EZRC SOL	Blue
Switch single pole connector	Stranded	<input type="checkbox"/> EZSPSWSTR	Yellow
Switch single pole connector	Solid	<input type="checkbox"/> EZSPSW SOL	Yellow
Switch 3-way connector	Stranded	<input type="checkbox"/> EZ3WSWSTR	Yellow
Switch 3-way connector	Solid	<input type="checkbox"/> EZ3WSW SOL	Yellow

## SPECIFICATIONS

<b>Electrical</b>	<b>Dielectric voltage:</b> Withstands 2000V per UL 498 <b>Frequency:</b> 60 Hz; Voltage: 125 V/AC (receptacle); 120/277 V/AC (switch) <b>Amperage:</b> 15A/20A
<b>Testing &amp; code compliance</b>	cULus Listed to UL 498 (EZRC) UL file no. E15058, UL 20 (EZSW) UL file no. E18704, applicable CSA requirements and NOM certified
<b>Environmental</b>	<b>Flammability:</b> Meets UL 94 requirements; V2 rated <b>Temperature rating:</b> -20°C to 60°C (-4°F to 140°F)
<b>Mechanical</b>	<b>Voltage ratings:</b> Permanently marked on device

## MATERIALS


<b>Housing</b>	Top: Polycarbonate Bottom: Polycarbonate
<b>Contacts</b>	0.024" Thick phosphor bronze C51900



EZSPSWSTR

EZ3WSWSTR

EZRCSTR



Mid-Install

Full-Install





EZ Link modular devices...

Fast to the finish

# We make what matters work.\*

\* At Eaton, we believe that power is a fundamental part of just about everything people do. Technology, transportation, energy and infrastructure-these are things the world relies on every day. That's why Eaton is dedicated to helping our customers find new ways to manage electrical, hydraulic and mechanical power more efficiently, safely and sustainably. To improve people's lives, the communities where we live and work, and the planet our future generations depend upon. Because that's what really matters. And we're here to make sure it works.

See more at [Eaton.com/whatmatters](https://Eaton.com/whatmatters)



For more information  
[Eaton.com/EZLink](https://Eaton.com/EZLink)

Electrical Sector  
1123 Hwy 74 S  
Peachtree City, GA 30269  
United States  
[Eaton.com](https://Eaton.com)  
[Eaton.com/EZLink](https://Eaton.com/EZLink)

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
[Eaton.com](https://Eaton.com)

© 2024 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. BR620030EN  
September 2024

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
[EatonCanada.ca](https://EatonCanada.ca)  
[Eaton.com/EZLink](https://Eaton.com/EZLink)

Eaton is a registered trademark.

All other trademarks are property  
of their respective owners.

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlan Km 17.8 s/n  
Col. Villa Jardin esq.  
Cerrada 8 de Mayo  
Cuautitlan, Mexico CP 54800  
Mexico  
[Eaton.mx](https://Eaton.mx)  
[Eaton.com/EZLink](https://Eaton.com/EZLink)

Follow us on social media to get the  
latest product and support information.



Powering Business Worldwide