


		TIME-CURRENT CHARACTERISTIC CURVES MINIMUM MELT 15.0 KV ELF™ DROPOUT FUSE	
		Tests made at LOW Volts ac at HIGH pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1981 (R1982) MINIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE PLUS	
DRAWN BY RJKH DATE 3-2-00 REPLACES 5/96 REV 04 DWG NO. 42 3921 B 00	CHK'D DATE REV 04 REG NO. 19586	THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.	
NOTE: 95KV BIL MOUNTED FUSES AVAILABLE IN 6 THROUGH 20AMP. 125KV BIL MOUNTED FUSES AVAILABLE IN 6 THROUGH 50AMP.		Reference Data R240-91-43 Page 1 of 2	



		TIME-CURRENT CHARACTERISTIC CURVES MAXIMUM CLEAR 15.0 KV ELF™ DROPOUT FUSE	
		Tests made at HIGH Volts ac at LOW pf at 25°C with no initial load Standards used as basis for data: ANSI C37.47-1981 (R1982) MAXIMUM TEST POINTS PLOTTED SO VARIATIONS SHOULD BE MINUS	
DRAWN BY RJKH DATE 3-2-00 REPLACES 5/96 REV 04 DWG NO. 42 3921 B 00	CHK'D DATE REV 04 REG NO. 19586	THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.	
NOTE: 95KV BIL MOUNTED FUSES AVAILABLE IN 6 THROUGH 20AMP. 125KV BIL MOUNTED FUSES AVAILABLE IN 6 THROUGH 50AMP.		Reference Data R240-91-43 Page 2 of 2	