

Caratteristiche



La foto è a scopo illustrativo



Eaton BK/GMC-V-80-R

Eaton GMC Series Medium time-delay fuse
0.08A, 250 Vac, 32 Vdc (self certified), BK-
GMC-V-80-R

Specifiche generali

PRODUCT NAME	Eaton Bussmann series GMC time-delay fuse
CATALOG NUMBER	BK/GMC-V-80-R
UPC	051712232319
PRODUCT LENGTH/DEPTH	20 mm
PRODUCT HEIGHT	5 mm
PRODUCT WIDTH	5 mm
PRODUCT WEIGHT	1.97 g
COMPLIANCES	CE Marked RoHS Compliant



Powering Business Worldwide

Caratteristiche prodotto

USED WITH	Axial leads
AMPERAGE RATING	0.08A
INTERRUPT RATING	35 AIC at 250 Vac 10 kAIC at 125 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 2 min at 200%
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	100
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Risorse

NOME DEL PROGETTO:

NUMERO DEL PROGETTO:

PREPARATO DA:

DATA:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublino 4, Irlanda
Eaton.com

© 2026 Eaton. Tutti i diritti riservati.

Seguici sui social media per avere
informazioni aggiornate sui prodotti
e sull'assistenza.

