

KV	AMP RANGE
8.3	130-280
15.5	130-250
23.0	130-200

FUSES MADE UP OF 2 SMALLER UNITS OF EQUAL RATING IN A PARALLEL MOUNTING




TIME-CURRENT CHARACTERISTIC CURVES

MINIMUM MELT TIME-CURRENT CHARACTERISITC CURVES
8.3, 15.5 & 23kV X-LIMITER FULL RANGE PARALLEL MOUNTED FUSE

DRAWN BY	RJC	CHK'D	
DATE	1-15-96	DATE	
REPLACES	5/88	REV	01
		REQ. NO.	
DWG NO.	TCC304 M		

Tests made at RATED Volts ac at LOW pf at 25°C with no initial load
Standards used as basis for data: ANSI C37.47-1981
MINIMUM TEST POINTS PLOTTED 50 VARIATIONS SHOULD BE PLUS
THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.



KV	AMP RANGE
8.3	130-280
15.5	130-250
23.0	130-200

FUSES MADE UP OF 2 SMALLER UNITS OF EQUAL RATING IN A PARALLEL MOUNTING

EATON		TIME-CURRENT CHARACTERISTIC CURVES	
		MAXIMUM CLEAR TIME-CURRENT CHARACTERISTIC CURVES 8.3, 15.5 & 23kV X-LIMITER FULL RANGE PARALLEL MOUNTED FUSE	
DRAWN BY	RJC	CHK'D	
DATE	1-15-96	DATE	
REPLACES	5/88 REV 01	REQ. NO.	
DWG NO.	TCC304 C	THIS DRAWING WAS PRODUCED ON A CAD SYSTEM, ANY MANUAL REVISION WILL VOID IT.	