



Eaton

RT2SSEO200WLS3HIPB

Eaton Roundtech Medium Surface Safety
EFOCUS WLS 200 MNM 3H IP65 Black

Specificații generale

PRODUCT NAME	Eaton RoundTech MSSEO surface emergency luminaire
CATALOG NUMBER	RT2SSEO200WLS3HIPB
EAN	3660191823337
PRODUCT LENGTH/DEPTH	138 mm
PRODUCT HEIGHT	48 mm
PRODUCT WIDTH	138 mm
PRODUCT WEIGHT	0.295 kg
CERTIFICATIONS	CE

Specificații corpuri de iluminat de urgență

COLOR HOUSING	Black
COLOR TEMPERATURE - MAX	5700 K
COLOR TEMPERATURE - MIN	5700 K
CONNECTION TYPE	Plug-in connection
CONSTANT LIGHT OUTPUT (CLO)	No
ENERGY EFFICIENCY CLASS	A
EXCHANGEABLE CONTROL GEAR	No
FUNCTION	Escape route lighting
IMPACT STRENGTH	IK04
LAMP HOLDER	None
LAMP TYPE	LED not exchangeable
LIGHT DISTRIBUTOR	Focal lens
LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D	No
LUMINOUS FLUX IN STANDBY MODE	60 lm
MATERIAL COVER	Without cover
MATERIAL HOUSING	Plastic
MAX. SYSTEM POWER	1.1 W
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
MOUNTING METHOD	Ceiling surface mounting
NOMINAL OPERATION TIME - MAX	3 hour
NOMINAL OPERATION TIME - MIN	3 hour
NOMINAL VOLTAGE AC - MAX	230 V
NOMINAL VOLTAGE AC - MIN	230 V
NUMBER OF LIGHTING HEADS	1
NUMBER OF POLES (NUMERIC)	3
PICTOGRAM INCLUDED	No
POWER FACTOR	0.61
POWER SUPPLY SYSTEM	Peripheral (individual battery)
RAL-NUMBER (SIMILAR)	9005

Specificații accesorii mecanice

BATTERY QUALITY	Lithium-ion
COLOR TEMPERATURE - MIN	5700 K
CONNECTION TYPE	Plug-in connection
CONSTANT LIGHT OUTPUT (CLO)	No
DEGREE OF PROTECTION	IP65
ENERGY EFFICIENCY CLASS	A
EXCHANGEABLE CONTROL GEAR	No
FUNCTION	Escape route lighting
IMPACT STRENGTH	IK04
LAMP HOLDER	None
LAMP TYPE	LED not exchangeable
LIGHT DISTRIBUTOR	Focal lens
LUMINOUS FLUX IN STANDBY MODE	60 lm
MATERIAL COVER	Without cover
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
MOUNTING METHOD	Ceiling surface mounting
NOMINAL OPERATION TIME - MAX	3 hour
NOMINAL OPERATION TIME - MIN	3 hour
NUMBER OF LIGHTING HEADS	1
POWER FACTOR	0.61
POWER SUPPLY SYSTEM	Peripheral (individual battery)
RAL-NUMBER (SIMILAR) HOUSING	9005
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	200 lm
SUITABLE FOR CONTINUOUS CIRCUIT	No
SUITABLE FOR STANDBY SWITCHING	No
MAX. SYSTEM POWER	1.1 W
TYPE OF WIRING	Suitable for through wiring
VOLTAGE TYPE	AC
WITH LIGHT SOURCE	Yes
WITH REMOTE CONTROL	No

HOUSING	
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	200 lm
SUITABLE FOR CONTINUOUS CIRCUIT	No
SUITABLE FOR STANDBY SWITCHING	No
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Suitable for through wiring
VOLTAGE TYPE	AC
WITH LIGHT SOURCE	Yes
WITH REMOTE CONTROL	No
WITH REMOTE SWITCH CONNECTION	No

WITH REMOTE SWITCH CONNECTION	No
----------------------------------	----

Resurse

DENUMIREA PROIECTULUI:
NUMĂRUL PROIECTULUI:
PREGĂTIT DE:
DATA:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irlanda
Eaton.com

© 2026 Eaton. Toate drepturile rezervate

Urmăriți-ne pe rețelele de socializare
pentru a obține cele mai noi
informații despre produse și
asistență.

