
DO NOT SCALE



- 1/ TYPE SM87 SL3
- 2/ CERTIFICATION No. Baseefa03ATEX0222 EExd IIC T4 (FILAMENT)

EExd IIC T6 (LED, XENON & FLUORESCENT)

- 3/ WE IGHT LED 3.8 ± 0.2 KG HXB - 3.8 ± 0.2 KG LU1 - 3.7 ± 0.2 KG LU3 - 3.5 ± 0.2 KG BACKPLATE - 0.3/0.1 KG
- 4/ MATERIAL STAINLESS STEEL GRADE 316/ANC 4B TO BS3146:1975

 OR MARINE GRADE ALLOY GRADE LM25TF TO BS1490:1988.
- 5/ FUNCTION/TAG LETTER SIZE 5mm MAX.
- 6/ TERMINALS SUITABLE FOR UP TO 1.5mm SQ. CABLE
- 7/ CABLE ENTRIES AVAILABLE AT "1" "2" "3" "4" "5" & "6"
- 8/ POSITIONS "A" "B" "C" ANY COMBINATION OF LED/HXB/LU1/LU3
- 9/ BACKPLATE THICKNESS 2.5/1.5mm



Cooper MEDC Ltd, Unit B, Sutton Parkway, Oddicroft Lane, Sutton-in-Ashfield, Nottinghamshire, NG17 5FB, U.K. Tel:+ 44 (0) 1623 444400 web: www.coopermedc.com

DESIGNERS & MANUFACTURERS
OF ELECTRICAL & ELECTRONIC
EQUIPMENT & SYSTEMS FOR
HAZARDOUS AREAS

Н

ISSUES	S S S S S S S S S S S S S S S S S S S	GENERAL TOLERANCES	NCES IN MILLIMETRES UNLESS	THIS DRAWING IS CONFIDENTIAL AND IS THE PROPERTY OF MEDC AND MUST NOT BE REPRODUCED EITHER WHOLLY OR PARTLY. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHT ARE RESERVED.	DRAWN BY: C. FOSTER	DATE: 20-11-92	TITLE SM87 SL3	
	-06-07 -11-08 -11-08 -11-08 -11-08 -03-14	U.O.S			CHECKED BY:	DATE:		
		LINEAR: ±0.25			S.J.M.	20-11-92	GENERAL ARRANGEMENT	
			REMOVE ALL BURRS AND SHARP EDGES		APPROVED BY:	DATE:		
	28 13 20 20 20	ANGULAR: ±0.5°			S.J.M.	20-11-92		_
		SURFACE FINISH: V	MACHINE SYMBOLS THUS Vµm		SCALE:	SIZE A4	DRG No. S-051-01-03	ISSUE

