

# V-CG-SLP 350

LED supply- and monitoring module




## V-CG-SLP 350

- Suitable for operation at cold ambient conditions down to  $-40^{\circ}\text{C}$ , e.g. in cold storage facilities
- Low operating costs due to decreased standby losses  $< 0.5\text{ W}$
- Minimized dimensions on the basis of conventional T5 EVG cross section (H x W: 21 x 30 mm) for an eased mounting in narrow luminaires
- Without protective conductor connection. For the use in luminaires with insulation class I or II
- Variable mounting possibilities for different mounting positions (horizontal or sidewise upright)
- Avoidance of installation failures due to a mains connection being protected against polarity reversal
- Shortened inspection effort due to the CEWA GUARD- and STAR+-Technology: Automatic function monitoring of up to 20 luminaires per circuit
- Reduced installation costs due to STAR-Technology: Freely programmable mixed operation of the switching modes per luminaire in one circuit
- Reduced installation expenditures as no additional data line to the luminaires is needed


V-CG-SLP 350




Dimensions in mm



Module housing



Dimensions in mm



### Primary side (data valid for full load with 8 LEDs)

Rated voltage ranges	220- 240 V, 50/60 Hz / 176- 275 V DC
Standby power loss	$< 0.5\text{ W}$ (230 V / 50 Hz)
Current consumption 220 V DC	43 mA
Power input	11.6 VA / 10.7 W
Power factor $\lambda$	0.9
Inrush current	$\leq 3.0\text{ A}$
Operating frequency	30 kHz- 450 kHz
Connection terminals	Clamp terminals $2.5\text{ mm}^2$ / reverse-polarity protected

### Secondary side

Output current	350 mA +/- 10%
Output voltage	30 V DC (open-circuit operation) +/- 10%
Output voltage in operation	25 V +/- 10% (8 LEDs)
Lamp load	1-8 LEDs (rated current 350 mA), series connection (UF = 2.85 ... 3.12 V)
Output power (max.)	8.75 W
Connection terminals	$1.5\text{ mm}^2$ / not reverse-polarity protected
Maximum line length	0.5 m (module – LED)
Type of mounting	To be mounted in luminaires with protection category I or II
Degree of protection	IP20
Permissible ambient temperature	$t_a = -40^{\circ}\text{C}$ to $+50^{\circ}\text{C}$
Maximal permissible test point temperature	$t_c = 70^{\circ}\text{C}$
Dimensions in mm (L x H x W)	110 x 30 x 21
Housing material / Colour	Flame retardant polycarbonate / grey
Weight	0.042 kg
Luminous flux $\Phi_E/\Phi_N$ at the end of rated operating time (EBLF)	100 %

### Ordering details

Scope of supply	Order No.
V-CG-SLP 350	40071355020
Module housing with strain relief	40071352765