

Installation Instructions



0905
DoP0252

EN54-18:2005 + AC: 2007

Specifications

Output Relays	Min	Nom	Max
Switching Voltage		24 VDC	30 VDC
240V ac Contact Rating			10 A
30V dc Contact Rating			10 A

Standards

EN54 : Pt18

Compatibility

Suitable for use with Eaton Conventional Systems

Physical

Dimensions	150 x 89 x 58 (mm)
Weight	0.24kg
Ingress Protection	IP30


Installation

1. Separate the two halves of the unit.
2. Drill out (or knock out) the required cable entries in the surface mounting back-box.
3. Fit the back-box in position and pass the wires into it.
4. Connect the unit according to the diagram below.
5. Recommended Loop Cable Type: FIRETUF, FP200, MICC

Note: There are no serviceable parts so no maintenance procedures apply.



RELAY 1 RELAY 2



Compatible
Control
Panel

24V dc OUTPUT



Powering Business Worldwide

Eaton Electrical Systems Ltd.
Wheatley Hall Road
Doncaster
DN2 4NB
TEL: +44 (0) 1302 303303
FAX: +44 (0) 1302 367155

Eaton
EMEA Headquarters
Route de la Longeraie 7
1110 Morges, Switzerland
Eaton.eu
TEL: +44 (0) 1302 321541
FAX: +44 (0) 1302 303220
Firesales@eaton.com
Firetechsupport@eaton.com

© 2019 Eaton
All Rights Reserved
Eaton is a registered trademark.

All trademarks are property
of their respective owners.
www.Eaton.com

TECHNICAL DATA 25-16722-A November 2019