

Specifications



Photo is representative



Eaton 277571

Eaton Moeller® series DILM Contactor, 3 pole, 380 V 400 V 7.5 kW, 1 N/O, 48 V 50 Hz, AC operation, Spring-loaded terminals

General specifications

PRODUCT NAME	Eaton Moeller® series DILM contactor
CATALOG NUMBER	277571
EAN	4015082775711
MODEL CODE	DILMC17-10(48V50HZ)
PRODUCT LENGTH/DEPTH	97 mm
PRODUCT HEIGHT	85 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.433 kg
CERTIFICATIONS	UL 508 CSA Class No.: 2411-03, 3211-04 VDE 0660 IEC/EN 60947-4-1 CSA File No.: 012528 CSA-C22.2 No. 14-05 CE IEC/EN 60947 UL File No.: E29096 CSA UL UL Category Control No.: NLDX
CATALOG NOTES	Contacts according to EN 50012

Features & Functions

NUMBER OF POLES	Three-pole
------------------------	------------

General

APPLICATION	Contactors for Motors
FRAME SIZE	FS2
LIFESPAN, MECHANICAL	10,000,000 Operations (AC operated)
OPERATING FREQUENCY	5000 mechanical Operations/h (AC operated)
OVERVOLTAGE CATEGORY	III
POLLUTION DEGREE	3
PRODUCT CATEGORY	Contactors
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	8000 V AC
RESISTANCE PER POLE	2.7 mΩ
SUITABLE FOR	Also motors with efficiency class IE3
UTILIZATION CATEGORY	AC-3: Normal AC induction motors: starting, switch off during running AC-4: Normal AC induction motors: starting, plugging, reversing, inching AC-1: Non-inductive or slightly inductive loads, resistance furnaces
VOLTAGE TYPE	AC

Ambient conditions, mechanical

SHOCK RESISTANCE

7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
6.9 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms
3.5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms
5.3 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms
10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

Climatic environmental conditions

AMBIENT OPERATING TEMPERATURE - MIN -25 °C

AMBIENT OPERATING TEMPERATURE - MAX 60 °C

AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN 25 °C

AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX 40 °C

AMBIENT STORAGE TEMPERATURE - MIN 40 °C

AMBIENT STORAGE TEMPERATURE - MAX 80 °C

CLIMATIC PROOFING
Damp heat, cyclic, to IEC 60068-2-30
Damp heat, constant, to IEC 60068-2-78

Electro Magnetic Compatibility

EMITTED INTERFERENCE According to EN 60947-1

INTERFERENCE IMMUNITY According to EN 60947-1

Terminal capacities

TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)
2 x (0.75 - 1.5) mm², Control circuit cables, Spring-loaded terminals
2 x (0.75 - 10) mm², Main cables
1 x (0.75 - 1.5) mm², Control circuit cables, Spring-loaded terminals
1 x (0.75 - 16) mm², Main cables

TERMINAL CAPACITY (FLEXIBLE)
2 x (0.75 - 2.5) mm², Control circuit cables, Spring-loaded terminals
1 x (0.75 - 2.5) mm², Control circuit cables, Spring-loaded terminals

TERMINAL CAPACITY (SOLID)
1 x (0.75 - 16) mm², Main cables
1 x (0.75 - 2.5) mm², Control circuit cables, Spring-loaded terminals
2 x (0.75 - 10) mm², Main cables
2 x (0.75 - 2.5) mm²,

	Control circuit cables, Spring-loaded terminals
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 14, Control circuit cables, Spring-loaded terminals Single 18 - 6, double 18 - 8, Main cables
TERMINAL CAPACITY (STRANDED)	1 x 16 mm ² , Main cables
STRIPPING LENGTH (MAIN CABLE)	10 mm
STRIPPING LENGTH (CONTROL CIRCUIT CABLE)	10 mm
SCREW SIZE	M5, Terminal screw, Main cables
SCREWDRIVER SIZE	2, Terminal screw, Main cables, Pozidriv screwdriver 0.8 x 5.5/1 x 6 mm, Terminal screw, Main cables, Standard screwdriver 3.5 mm, Spring-loaded terminals, Control circuit cables
TIGHTENING TORQUE	3.2 Nm, Screw terminals, Main cables

Electrical Rating

RATED BREAKING CAPACITY AT 220/230 V	170 A
RATED BREAKING CAPACITY AT 380/400 V	170 A
RATED BREAKING CAPACITY AT 500 V	170 A
RATED BREAKING CAPACITY AT 660/690 V	120 A
RATED OPERATIONAL CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V	40 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	18 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	18 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 440 V	18 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	18 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	12 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 220 V, 230 V, 240 V	10 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 400 V	10 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 500 V	10 A
RATED OPERATIONAL CURRENT (IE) AT AC-4, 660 V, 690 V	8 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 60 V	35 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 110 V	35 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, 220 V	35 A
RATED INSULATION VOLTAGE (UI)	690 V
RATED OPERATIONAL	40 A

Short-circuit rating

SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	125 A, max. Fuse, SCCR (UL/CSA) 125 A, max. CB, SCCR (UL/CSA) 5 kA, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 480 V)	10/100 kA, Fuse, SCCR (UL/CSA) 125/70 A, Class J, max. Fuse, SCCR (UL/CSA) 50/32 A, max. CB, SCCR (UL/CSA) 10/65 kA, CB, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (HIGH FAULT AT 600 V)	125/70 A, Class J, max. Fuse, SCCR (UL/CSA) 50/32 A, max. CB, SCCR (UL/CSA) 10/100 kA, Fuse, SCCR (UL/CSA) 10/22 kA, CB, SCCR (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 400 V	63 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 1 COORDINATION) AT 690 V	50 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 400 V	35 A gG/gL
SHORT-CIRCUIT PROTECTION RATING (TYPE 2 COORDINATION) AT 690 V	35 A gG/gL

CURRENT (IE) AT AC-1, 380 V, 400 V, 415 V	
RATED OPERATIONAL POWER AT AC-3, 240 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	7.5 kW
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	10 kW
RATED OPERATIONAL POWER AT AC-4, 220/230 V, 50 HZ	2.5 kW
RATED OPERATIONAL POWER AT AC-4, 240 V, 50 HZ	3 kW
RATED OPERATIONAL POWER AT AC-4, 415 V, 50 HZ	5 kW
RATED OPERATIONAL POWER AT AC-4, 440 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-4, 500 V, 50 HZ	6 kW
RATED OPERATIONAL POWER AT AC-4, 660/690 V, 50 HZ	6.5 kW
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V

Conventional thermal current	
CONVENTIONAL THERMAL CURRENT ITH (1-POLE, ENCLOSED)	80 A
CONVENTIONAL THERMAL CURRENT ITH (3-POLE, ENCLOSED)	32 A
CONVENTIONAL THERMAL CURRENT ITH AT 55°C (3-POLE, OPEN)	37 A
CONVENTIONAL THERMAL CURRENT ITH OF MAIN CONTACTS (1- POLE, OPEN)	88 A

Switching capacity	
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	40 A, Maximum motor rating (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	A600, AC operated (UL/CSA) P300, DC operated (UL/CSA)

Switching time

ARCING TIME 10 ms

SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MIN 16 ms

SWITCHING TIME (AC OPERATED, MAKE CONTACTS, CLOSING DELAY) - MAX 22 ms

SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MIN 8 ms

SWITCHING TIME (AC OPERATED, MAKE CONTACTS, OPENING DELAY) - MAX 14 ms

Magnet system

DROP-OUT VOLTAGE AC operated: 0.6 - 0.3 x UC, AC operated

DUTY FACTOR 100 %

PICK-UP VOLTAGE 0.8 - 1.1 V AC x Uc

POWER CONSUMPTION, PICK-UP, 50 HZ 52 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz

POWER CONSUMPTION, PICK-UP, 60 HZ 67 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz

POWER CONSUMPTION, SEALING, 50 HZ 2.1 W, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz
7.1 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 50 Hz

POWER CONSUMPTION, SEALING, 60 HZ 8.7 VA, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz
2.1 W, Dual-frequency coil in a cold state and 1.0 x Us, at 60 Hz

RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN 48 V

RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX 48 V

RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN 0 V

RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX 0 V

RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN 0 V

RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX 0 V

Motor Rating

ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	2 HP
---	------

ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	5 HP
---	------

ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	3 HP
---	------

ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	5 HP
---	------

ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	10 HP
---	-------

ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	15 HP
---	-------

Contacts

NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
---	---

NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
---	---

NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	1
---	---

Communication

CONNECTION	Spring-loaded terminals
------------	-------------------------

CONNECTION TO SMARTWIRE-DT	No
-------------------------------	----

Safety

SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140 440 V AC, Between coil and contacts, According to EN 61140
----------------	---

Special purpose ratings

SPECIAL PURPOSE RATING OF BALLAST ELECTRICAL DISCHARGE LAMPS	40 A (480V 60Hz 3phase, 277V 60Hz 1phase) 40 A (600V 60Hz 3phase, 347V 60Hz 1phase)
SPECIAL PURPOSE RATING OF DEFINITE PURPOSE RATING	108 A, LRA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 18 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)
SPECIAL PURPOSE RATING OF ELEVATOR CONTROL	7.5 HP, 480 V 60 Hz 3-ph, (UL/CSA) 3 HP, 200 V 60 Hz 3-ph, (UL/CSA) 3 HP, 240 V 60 Hz 3-ph, (UL/CSA) 10 HP, 600 V 60 Hz 3-ph, (UL/CSA) 11 A, 200 V 60 Hz 3-ph, (UL/CSA) 11 A, 480 V 60 Hz 3-ph, (UL/CSA) 11 A, 600 V 60 Hz 3-ph, (UL/CSA) 9.6 A, 240 V 60 Hz 3-ph, (UL/CSA)
SPECIAL PURPOSE RATING OF REFRIGERATION CONTROL (CSA ONLY)	40 A, FLA 480 V 60 Hz 3phase; (CSA) 180 A, LRA 600 V 60 Hz 3phase; (CSA) 30 A, FLA 600 V 60 Hz 3phase; (CSA) 240 A, LRA 480 V 60 Hz 3phase; (CSA)
SPECIAL PURPOSE RATING OF RESISTANCE AIR HEATING	40 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) 40 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA)
SPECIAL PURPOSE RATING OF TUNGSTEN INCANDESCENT LAMPS	40 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) 40 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA)

Design verification

EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	2.1 W
HEAT DISSIPATION CAPACITY PDISS	0 W
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	18 A
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC	Is the panel builder's responsibility.

STRENGTH	
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

[Product Range Catalog](#)
[Switching and protecting motors](#)

CATALOGS [eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[SmartWire-DT Catalog](#)

CHARACTERISTIC CURVE [eaton-contactors-switch-dilm-characteristic-curve.eps](#)

[eaton-contactors-switch-dilm-characteristic-curve-002.eps](#)

[eaton-contactors-component-dilm-characteristic-curve-003.eps](#)

[eaton-contactors-mounting-dilm-dimensions.eps](#)

[eaton-contactors-mounting-dilm-dimensions-002.eps](#)

DRAWINGS [eaton-contactors-contact-dimensions-210x202.eps](#)

[eaton-contactors-dimensions-210t014.eps](#)

[eaton-contactors-dilm-3d-drawing-010.eps](#)

[eaton-general-ie-ready-dilm-contactor-standards.eps](#)

ECAD MODEL [ETN.277571.edz](#)

INSTALLATION INSTRUCTIONS [IL03407014Z2021_09.pdf](#)

INSTALLATION VIDEOS [WIN-WIN with push-in technology](#)

MCAD MODEL [DA-CD-dil mc17 38](#)

[DA-CS-dil mc17 38](#)

SYSTEM OVERVIEW [eaton-contactors-dilm-contactor-system-overview.eps](#)

WIRING DIAGRAMS [eaton-contactors-contact-dilm-wiring-diagram.eps](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

