

# Primary Unit Substations Secondary 1000 V & Above

## Contents

### Primary Unit Substations Secondary 1000 V & Above

#### Primary Liquid-Type Substations

General Description ..... 13.0-2

Layout Dimensions ..... 13.0-4

#### Primary Dry-Type Substations

General Description ..... 13.0-9

Layout Dimensions ..... 13.0-10


#### Dry/Liquid-Type Transformers

Technical Data ..... 13.0-13

#### Specifications

See Eaton's *Product Specification Guide*, available on CD or on the Web.

|                   |                      |                         |
|-------------------|----------------------|-------------------------|
| CSI Format: ..... | 1995                 | 2010                    |
|                   | <b>Section 16312</b> | <b>Section 26 11 13</b> |



*Primary Unit Substation Transformer—Liquid-Filled*

## General Description

### General Description

#### Definition

A primary unit substation is a close-coupled assembly consisting of enclosed primary high voltage equipment, three-phase power transformer and enclosed secondary medium voltage equipment. The following electrical ratings are typical:

- Primary voltage: 6.9–69 kV
- Transformer kVA: 500–20,000 kVA
- Secondary voltage: 2.4 kV–34.5 kV

A primary unit substation is defined in the following standards:

- NEMA® Standard No. 201-1982
- IEEE® Standard No. 100-1977

Primary unit substations are used to step down utility distribution voltages to in-plant distribution voltages.

Primary unit substation transformers are designed, manufactured and tested in accordance with applicable IEEE standards.


#### Advantages

As a result of locating power transformers and their close-coupled equipment as close as possible to the areas of load concentration, the secondary distribution cables or busways are kept to minimum lengths. This concept has obvious advantages such as:

- Reduced power losses
- Improved voltage regulation
- Improved service continuity
- Reduced exposure to faults
- Increased flexibility
- Minimum installation cost
- Efficient space utilization

Additional advantages of Eaton's unit substations in this unified approach are:

- Single-source responsibility
- Complete electrical and mechanical control over coordination of the three close-coupled sections
- Availability of all switchgear types as secondaries gives broad application flexibility
- Modern design
- Composite assembly retains proven safety and integrity of each of its three major parts



*Primary Unit Substation Transformer—Liquid-Filled*

#### Easier to Specify

Standardization through IEEE standards results in proven designs with complete accessory equipment and features.

#### Highest Short-Circuit Strength

Highly researched and thoroughly tested designs provide the short-circuit strength necessary to withstand the repeated large short-circuit currents that are available in modern systems.

#### Easier Handling and Reduced Maintenance

Compact designs reduce the cost of rigging and hauling and require smaller installation space. Straight-forward design and simplified accessories reduce maintenance costs.

#### Ratings Available

##### kVA—Three-Phase:

- 6.9–69 kV (350 kV BIL and below)
- 500–20,000 kVA

##### Frequency:

- 60 Hz or 50 Hz

##### Transformer Fluids:

- Mineral oil
- Silicone fluid
- Envirotemp™ FR3™

**Note:** For additional information about insulating fluids, see **Tab 14, Pages 14.0-3–14.0-8**.

#### Primary and Secondary Equipment:

- Air terminal chamber (ATC)
- Load interrupter switchgear, Type MVS
- Metal-enclosed circuit breaker switchgear, Types MEB, MEF and MSB
- Metal-clad circuit breaker switchgear, Type VacClad-W
- Vacuum fault interrupter (VFI) — liquid-filled transformer only
- MV motor control assemblies, Type AMPGARD
- Cover-mounted bushings (liquid transformer only)
- Medium voltage busway



**Note:** For additional information about transformer applications and types of insulating fluids, see **Tab 14**.

**General Description**
**Standard Features—  
Liquid-Filled Transformer**

- ① Cover—welded to tank
- ② Cooling tubes (radiators)
- Note:** Radiator position and number of radiators will vary based upon design.
- ③ Bolted handhole on cover
- ④ Automatic resealing mechanical pressure relief device
- ⑤ HV bushing, three total, located in ANSI Segment 2
- ⑥ LV bushing, four total (wye connected), located in ANSI Segment 4

**Note:** HV and LV bushings may be cover mounted or left/right orientation may be reversed.

- ⑦ Z-bar flange
- ⑧ Lifting loops—two for lifting cover only
- ⑨ Lifting hooks—four for lifting complete unit
- ⑩ Jacking provisions on tank or base
- ⑪ Ground pad—two total
- ⑫ Drain valve—for combination lower filter press connection and complete drain with sampler
- ⑬ Base (may be flat or formed)
- ⑭ Control cabinet for alarm lead termination
- ⑮ Diagram instruction nameplate with warning nameplate
- ⑯ De-energized tap changer with padlock provisions
- ⑰ Liquid temperature indicator with maximum indicating hand
- ⑱ Upper valve for upper filter press connection
- ⑲ Magnetic liquid level gauge
- ⑳ Vacuum pressure gauge with air test and Sealedaire® valve


**Top View**

**Front View**
**Figure 13.0-1. Liquid-Filled Primary Unit Substation Transformer with Wall-Mounted HV and LV Bushings**

## Layout Dimensions

## Layout Dimensions




Figure 13.0-2. Outdoor Liquid-Filled Primary Unit Substations—Plan View

① Radiator position and number of radiators will vary based on design.

Table 13.0-1. Outdoor Dimension References

| Equipment   | Dimensions     | Reference                             |
|-------------|----------------|---------------------------------------|
| Transformer | W, D           | Pages 13.0-6 through 13.0-8           |
| MVC         | WS, DS         | Tab 10, Pages 10.1-25 through 10.1-41 |
| MVS         | WP, DP, WS, DS | Tab 8, Pages 8.0-18 through 8.0-28    |
| ME          | WP, DP, WS, DS | Tab 7, Pages 7.1-4 through 7.1-6      |
| MC          | WP, DP, WS, DS | Tab 5, Pages 5.5-1 through 5.5-41     |

## Transition Section or Throat and other Reference Dimensions

| Primary or Secondary Equipment | Three-Phase, Three-Wire or Four-Wire ② |        |    |         |        |
|--------------------------------|----------------------------------------|--------|----|---------|--------|
|                                | D1F                                    | D1R    | W1 | D2F     | D2R    |
| 5 kV MVC ②                     | —                                      | —      | 12 | —       | 21     |
| 5 kV MVS                       | 25.25 ③                                | —      | 20 | 25.25 ③ | —      |
| or ME                          | 25.25 ③                                | —      | 20 | 25.25 ③ | —      |
| 15 kV MC                       | —                                      | 16.5 ④ | 16 | —       | 16.5 ④ |
| 27 kV MVS                      | ⑤                                      | —      | 35 | ⑤       | —      |
| ME                             | ⑤                                      | —      | 35 | ⑤       | —      |
| MC ⑥                           | —                                      | —      | —  | —       | —      |
| 38 kV MVS                      | ⑤                                      | —      | 35 | ⑤       | —      |
| ME ⑥                           | —                                      | —      | —  | —       | —      |
| MC ⑤                           | —                                      | —      | —  | —       | —      |

② Four-wire connections are not available with MVC equipment.

③ For three-phase, four-wire, D1F and D2F are 30.25.

④ For three-phase, four-wire, D1R and D2R are 14.5.

⑤ Contact Eaton.

⑥ This product is not available for this voltage and configuration.

## Legend:

MVC = Medium Voltage Motor Control, Type AMPGARD

MVS = Medium Voltage Metal-Enclosed Switches, Type MVS


ME = Medium Voltage Metal-Enclosed Breakers, Type MEB, MEF, MSB

MC = Medium Voltage Metal-Clad Breaker Assemblies, Type VacClad-W

## Layout Dimensions

**Substation with Air Terminal Chamber (ATC)  
Utilization—Liquid-Filled Transformer**

A substation using one or two Air Terminal Chambers (ATCs) is different from a substation using close-coupling on both the primary and secondary sides. An ATC uses a cable connection on either the primary side, secondary side or both, and is placed between the transformer and the remotely mounted primary or secondary equipment.



**Figure 13.0-3. Liquid-Filled Indoor/Outdoor Using Air Terminal Chambers—Top View**

① Radiator position and number of radiators will vary based on design.

**Table 13.0-2. Primary or Secondary ATC or Transition Section—Dimensions in Inches (mm)**

| Voltage | Three-Phase, Three-Wire or Three-Phase, Four-Wire |                |                |                |
|---------|---------------------------------------------------|----------------|----------------|----------------|
| kV      | W <sub>1</sub>                                    | D <sub>P</sub> | W <sub>2</sub> | D <sub>S</sub> |
| 5 or 15 | 22.00 (558.8)                                     | 48.00 (1219.2) | 22.00 (558.8)  | 48.00 (1219.2) |
| 27      | 25.00 (635.0)                                     | 54.00 (1371.6) | 25.00 (635.0)  | 54.00 (1371.6) |
| 38      | 35.00 (889.0)                                     | 60.00 (1524.0) | 35.00 (889.0)  | 60.00 (1524.0) |

**Note:** Minimum ATC widths by kVA are listed in the table above. The width of any ATC can be expanded to allow for the installation of additional conduits. When calculating the area of the conduit opening, allow for a 2.00-inch (50.8 mm) lip around the entire perimeter of the ATC.

### Layout Dimensions

For special 55 °C rise units, bus duct throats and air terminal chambers, see **Notes 2 through 6** at bottom of page for dimensions that should be added to the table dimensions.

**Table 13.0-3. 65 °C Rise, Oil-Filled**  
**HV 6900D, 75 BIL**  
**LV 2400Y, 45 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |             |             |
|------------|-----------------|-------------------------|---------------------------|-------------|-------------|
|            |                 |                         | Height                    | Width       | Depth       |
| 500        | 4520 (2050)     | 120 (454)               | 92 (2336.8)               | 56 (1422.4) | 56 (1442.4) |
| 750        | 4750 (2155)     | 150 (568)               | 92 (2336.8)               | 56 (1422.4) | 56 (1442.4) |
| 1000       | 5590 (2536)     | 170 (644)               | 92 (2336.8)               | 59 (1498.6) | 59 (1498.6) |
| 1500       | 7380 (3348)     | 210 (795)               | 92 (2336.8)               | 67 (1701.8) | 67 (1701.8) |
| 2000       | 8890 (4032)     | 240 (908)               | 92 (2336.8)               | 70 (1778.0) | 70 (1778.0) |
| 2500       | 10,060 (4563)   | 260 (984)               | 92 (2336.8)               | 70 (1778.0) | 70 (1778.0) |
| 3000       | 11,110 (5039)   | 290 (1098)              | 95 (2413.0)               | 70 (1778.0) | 70 (1778.0) |
| 3750       | 13,200 (5987)   | 340 (1287)              | 95 (2413.0)               | 73 (1854.2) | 73 (1854.2) |
| 5000       | 18,020 (8174)   | 620 (2347)              | 113 (2870.2)              | 74 (1879.6) | 74 (1879.6) |

**Table 13.0-4. 65 °C Rise, Oil-Filled**  
**HV 13800D, 95 BIL**  
**LV 2400Y, 45 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 4840 (2195)     | 160 (606)               | 92 (2336.8)               | 56 (1422.4)  | 79 (2006.6)  |
| 1000       | 5720 (2595)     | 180 (681)               | 92 (2336.8)               | 59 (1498.6)  | 78 (1981.2)  |
| 1500       | 7370 (3343)     | 210 (795)               | 92 (2336.8)               | 65 (1651.0)  | 92 (2336.8)  |
| 2000       | 8760 (3973)     | 230 (871)               | 92 (2336.8)               | 68 (1727.2)  | 114 (2895.6) |
| 2500       | 9940 (4509)     | 260 (984)               | 92 (2336.8)               | 68 (1727.2)  | 125 (3175.0) |
| 3000       | 11,650 (5284)   | 350 (1325)              | 95 (2413.0)               | 70 (1778.0)  | 127 (3225.8) |
| 3750       | 13,330 (6046)   | 390 (1476)              | 95 (2413.0)               | 72 (1828.8)  | 127 (3225.8) |
| 5000       | 16,640 (7548)   | 480 (1817)              | 95 (2413.0)               | 75 (1905.0)  | 131 (3327.4) |
| 7500       | 30,300 (13,744) | 1220 (4618)             | 114 (2895.6)              | 113 (2870.2) | 138 (3505.2) |
| 10,000     | 34,830 (15,799) | 1230 (4656)             | 114 (2895.6)              | 118 (2997.2) | 139 (3530.6) |

**Table 13.0-5. 65 °C Rise, Oil-Filled**  
**HV 13800D, 95 BIL**  
**LV 4160Y, 60 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 5120 (2322)     | 170 (644)               | 92 (2336.8)               | 57 (1447.8)  | 79 (2006.6)  |
| 1000       | 5980 (2712)     | 180 (681)               | 92 (2336.8)               | 62 (1574.8)  | 81 (2057.4)  |
| 1500       | 7280 (3302)     | 210 (795)               | 92 (2336.8)               | 63 (1600.2)  | 100 (2540.0) |
| 2000       | 8700 (3946)     | 230 (871)               | 92 (2336.8)               | 65 (1651.0)  | 108 (2743.2) |
| 2500       | 10,290 (4667)   | 270 (1022)              | 92 (2336.8)               | 70 (1778.0)  | 114 (2895.6) |
| 3000       | 11,860 (5380)   | 320 (1211)              | 95 (2413.0)               | 73 (1854.2)  | 127 (3225.8) |
| 3750       | 13,410 (6083)   | 360 (1363)              | 95 (2413.0)               | 73 (1854.2)  | 129 (3276.6) |
| 5000       | 17,030 (7725)   | 520 (1968)              | 99 (2514.6)               | 75 (1905.0)  | 131 (3327.4) |
| 7500       | 29,720 (13,481) | 1140 (4315)             | 109 (2768.6)              | 113 (2870.2) | 140 (3556.0) |
| 10,000     | 35,790 (16,234) | 1310 (4959)             | 116 (2946.4)              | 117 (2971.8) | 143 (3632.2) |

- Notes:**
1. Dimensions are APPROXIMATE. NOT FOR CONSTRUCTION.
  2. For 55 °C units, add 5.00 inches (127.0 mm) to width dimension and 10 in (254.0 mm) to depth dimension.
  3. Add 9.00 inches (228.6 mm) to width dimension for each bus duct throat.
  4. Add 22.00 inches (558.8 mm) to width dimension for each 15 kV air terminal chamber.
  5. Add 25.00 inches (635.0 mm) to width dimension for each 27 kV air terminal chamber.
  6. Add 35.00 inches (889.0 mm) to width dimension for each 34.5 kV air terminal chamber.

**Table 13.0-6. 65 °C Rise, Oil-Filled**  
**HV 22900D, 150 BIL**  
**LV 2400Y, 45 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 5650 (2563)     | 220 (833)               | 92 (2336.8)               | 59 (1498.6)  | 81 (2057.4)  |
| 1000       | 6400 (2903)     | 220 (833)               | 92 (2336.8)               | 61 (1549.4)  | 87 (2209.8)  |
| 1500       | 8020 (3638)     | 250 (946)               | 92 (2336.8)               | 64 (1625.6)  | 101 (2565.4) |
| 2000       | 9500 (4309)     | 280 (1060)              | 92 (2336.8)               | 68 (1727.2)  | 101 (2565.4) |
| 2500       | 10,550 (4785)   | 300 (1136)              | 92 (2336.8)               | 70 (1778.0)  | 107 (2717.8) |
| 3000       | 12,000 (5443)   | 330 (1249)              | 95 (2413.0)               | 73 (1854.2)  | 127 (3225.8) |
| 3750       | 14,350 (6509)   | 450 (1703)              | 95 (2413.0)               | 73 (1854.2)  | 128 (3251.2) |
| 5000       | 19,110 (8668)   | 700 (2650)              | 117 (2971.8)              | 74 (1879.6)  | 129 (3276.6) |
| 7500       | 30,880 (14,007) | 1210 (4580)             | 117 (2971.8)              | 102 (2590.8) | 140 (3556.0) |
| 10,000     | 39,080 (17,726) | 1600 (6057)             | 124 (3149.6)              | 106 (2692.4) | 145 (3683.0) |

**Table 13.0-7. 65 °C Rise, Oil-Filled**  
**HV 22900D, 150 BIL**  
**LV 4160Y, 60 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 5660 (2567)     | 210 (795)               | 92 (2336.8)               | 58 (1473.2)  | 83 (2108.2)  |
| 1000       | 6640 (3012)     | 230 (871)               | 92 (2336.8)               | 62 (1574.8)  | 87 (2209.8)  |
| 1500       | 8000 (3629)     | 250 (946)               | 92 (2336.8)               | 64 (1625.6)  | 107 (2717.8) |
| 2000       | 9350 (4241)     | 290 (1098)              | 92 (2336.8)               | 66 (1676.4)  | 107 (2717.8) |
| 2500       | 10,860 (4926)   | 310 (1173)              | 92 (2336.8)               | 71 (1803.4)  | 107 (2717.8) |
| 3000       | 12,400 (5625)   | 340 (1287)              | 95 (2413.0)               | 73 (1854.2)  | 130 (3302.0) |
| 3750       | 14,500 (6577)   | 430 (1628)              | 95 (2413.0)               | 74 (1879.6)  | 130 (3302.0) |
| 5000       | 19,510 (8850)   | 720 (2725)              | 118 (2997.2)              | 74 (1879.6)  | 132 (3352.8) |
| 7500       | 30,270 (13,730) | 1120 (4240)             | 118 (2997.2)              | 101 (2565.4) | 143 (3632.2) |
| 10,000     | 38,140 (17,300) | 1500 (5678)             | 124 (3149.6)              | 105 (2667.0) | 146 (3708.4) |

**Table 13.0-8. 65 °C Rise, Oil-Filled**  
**HV 22900D, 150 BIL**  
**LV 12470Y, 95 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 6630 (3007)     | 250 (946)               | 92 (2336.8)               | 65 (1657.0)  | 64 (1625.6)  |
| 1000       | 7510 (3406)     | 280 (1060)              | 92 (2336.8)               | 66 (1676.4)  | 78 (1981.2)  |
| 1500       | 9040 (4100)     | 290 (1098)              | 92 (2336.8)               | 69 (1752.6)  | 88 (2235.2)  |
| 2000       | 10,110 (4586)   | 290 (1098)              | 92 (2336.8)               | 70 (1778.0)  | 96 (2438.4)  |
| 2500       | 11,670 (5788)   | 330 (1249)              | 92 (2336.8)               | 73 (1854.2)  | 106 (2692.4) |
| 3000       | 12,760 (5793)   | 350 (1325)              | 95 (2413.0)               | 74 (1879.6)  | 130 (3302.0) |
| 3750       | 15,280 (6931)   | 440 (1666)              | 95 (2413.0)               | 75 (1905.0)  | 133 (3378.2) |
| 5000       | 19,370 (8786)   | 650 (2461)              | 107 (2717.8)              | 76 (1930.4)  | 136 (3454.4) |
| 7500       | 30,850 (13,993) | 1180 (4467)             | 114 (2895.6)              | 100 (2540.0) | 139 (3530.6) |
| 10,000     | 38,320 (17,382) | 1450 (5489)             | 122 (3098.8)              | 104 (2641.6) | 143 (3632.2) |

## Layout Dimensions

For special 55 °C rise units, bus duct throats and air terminal chambers, see **Notes 2 through 6** at bottom of page for dimensions that should be added to the table dimensions.

**Table 13.0-9. 65 °C Rise, Oil-Filled  
HV 34400D, 200 BIL  
LV 2400Y, 45 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 7000 (3175)     | 330 (1249)              | 115 (2921.0)              | 67 (1701.8)  | 66 (1676.4)  |
| 1000       | 7720 (3502)     | 350 (1325)              | 115 (2921.0)              | 67 (1701.8)  | 79 (2006.6)  |
| 1500       | 9880 (4481)     | 380 (1438)              | 115 (2921.0)              | 69 (1752.6)  | 98 (2489.2)  |
| 2000       | 11,300 (5126)   | 410 (1552)              | 115 (2921.0)              | 71 (1803.4)  | 112 (2844.8) |
| 2500       | 12,880 (5842)   | 450 (1703)              | 115 (2921.0)              | 71 (1803.4)  | 122 (3098.8) |
| 3000       | 13,760 (6241)   | 460 (1741)              | 115 (2921.0)              | 72 (1828.8)  | 130 (3302.0) |
| 3750       | 16,030 (7271)   | 520 (1968)              | 115 (2921.0)              | 85 (2159.0)  | 136 (3454.4) |
| 5000       | 19,780 (8972)   | 660 (2498)              | 117 (2971.8)              | 100 (2540.0) | 138 (3505.2) |
| 7500       | 30,270 (13,730) | 1070 (4050)             | 129 (3276.6)              | 124 (3149.6) | 138 (3505.2) |
| 10,000     | 39,290 (17,822) | 1480 (5602)             | 136 (3454.4)              | 127 (3225.8) | 140 (3556.0) |

**Table 13.0-10. 65 °C Rise, Oil-Filled  
HV 34400D, 200 BIL  
LV 4160Y, 60 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 7230 (3279)     | 340 (1287)              | 115 (2921.0)              | 68 (1727.2)  | 67 (1701.8)  |
| 1000       | 8040 (3647)     | 360 (1363)              | 115 (2921.0)              | 68 (1727.2)  | 80 (2032.0)  |
| 1500       | 9920 (4500)     | 390 (1476)              | 115 (2921.0)              | 69 (1752.6)  | 94 (2387.6)  |
| 2000       | 11,700 (5307)   | 430 (1628)              | 115 (2921.0)              | 71 (1803.4)  | 116 (2946.4) |
| 2500       | 13,120 (5351)   | 460 (1741)              | 115 (2921.0)              | 73 (1854.2)  | 124 (3149.6) |
| 3000       | 14,400 (6532)   | 500 (1893)              | 115 (2921.0)              | 76 (1930.4)  | 128 (3251.2) |
| 3750       | 16,210 (7353)   | 540 (2044)              | 115 (2921.0)              | 77 (1955.8)  | 136 (3454.4) |
| 5000       | 20,490 (9294)   | 740 (2801)              | 124 (3149.6)              | 95 (2413.0)  | 139 (3530.6) |
| 7500       | 31,470 (14,275) | 1190 (4505)             | 133 (3378.2)              | 122 (3098.8) | 140 (3556.0) |
| 10,000     | 36,390 (16,506) | 1190 (4505)             | 132 (3352.8)              | 125 (3175.0) | 145 (3683.0) |

**Table 13.0-11. 65 °C Rise, Oil-Filled  
HV 34400D, 200 BIL  
LV 13800Y, 95 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 9110 (4132)     | 410 (1552)              | 115 (2921.0)              | 72 (1828.8)  | 63 (1600.2)  |
| 1000       | 9370 (4250)     | 390 (1476)              | 115 (2921.0)              | 72 (1828.8)  | 70 (1778.0)  |
| 1500       | 10,760 (4881)   | 410 (1552)              | 115 (2921.0)              | 72 (1828.8)  | 93 (2362.2)  |
| 2000       | 12,210 (5538)   | 450 (1703)              | 115 (2921.0)              | 72 (1828.8)  | 108 (2743.2) |
| 2500       | 13,600 (6169)   | 470 (1779)              | 115 (2921.0)              | 74 (1879.6)  | 109 (2768.6) |
| 3000       | 14,990 (6799)   | 510 (1931)              | 115 (2921.0)              | 77 (1955.8)  | 125 (3175.0) |
| 3750       | 16,590 (7585)   | 540 (2044)              | 115 (2921.0)              | 77 (1955.8)  | 137 (3479.8) |
| 5000       | 20,480 (9290)   | 710 (2688)              | 122 (3098.8)              | 94 (2387.6)  | 138 (3505.2) |
| 7500       | 32,220 (14,615) | 1050 (3975)             | 125 (3175.0)              | 123 (3124.2) | 139 (3530.6) |
| 10,000     | 38,460 (17,445) | 1350 (5110)             | 135 (3429.0)              | 124 (3149.6) | 148 (3759.2) |

- Notes:**
1. Dimensions are APPROXIMATE. NOT FOR CONSTRUCTION.
  2. For 55 °C units, add 5.00 inches (127.0 mm) to width dimension and 10 inches (254.0 mm) to depth dimension.
  3. Add 9.00 inches (228.6 mm) to width dimension for each bus duct throat.
  4. Add 22.00 inches (558.8 mm) to width dimension for each 15 kV air terminal chamber.
  5. Add 25.00 inches (635.0 mm) to width dimension for each 27 kV air terminal chamber.
  6. Add 35.00 inches (889.0 mm) to width dimension for each 34.5 kV air terminal chamber.

**Table 13.0-12. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 6900D, 75 BIL  
LV 2400Y, 45 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |             |              |
|------------|-----------------|-------------------------|---------------------------|-------------|--------------|
|            |                 |                         | Height                    | Width       | Depth        |
| 750        | 4930 (2236)     | 160 (606)               | 87 (2209.8)               | 48 (1219.2) | 76 (1930.4)  |
| 1000       | 5940 (2694)     | 180 (681)               | 87 (2209.8)               | 52 (1320.8) | 92 (2336.8)  |
| 1500       | 7690 (3488)     | 220 (833)               | 87 (2209.8)               | 59 (1498.6) | 95 (2413.0)  |
| 2000       | 9270 (4205)     | 250 (946)               | 87 (2209.8)               | 62 (1574.8) | 107 (2717.8) |
| 2500       | 10,630 (4822)   | 280 (1060)              | 87 (2209.8)               | 62 (1574.8) | 112 (2844.8) |
| 3000       | 12,280 (5570)   | 340 (1287)              | 87 (2209.8)               | 63 (1600.2) | 121 (3073.4) |
| 3750       | 14,540 (6618)   | 380 (1438)              | 87 (2209.8)               | 67 (1701.8) | 122 (3098.8) |
| 5000       | 18,620 (8453)   | 580 (2196)              | 98 (2489.2)               | 68 (1727.2) | 123 (3124.2) |

**Table 13.0-13. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 13800D, 95 BIL  
LV 2400Y, 45 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 5010 (2272)     | 160 (606)               | 87 (2209.8)               | 48 (1219.2)  | 79 (2006.6)  |
| 1000       | 6090 (2762)     | 180 (681)               | 87 (2209.8)               | 53 (1346.2)  | 82 (2082.8)  |
| 1500       | 7730 (3506)     | 220 (833)               | 87 (2209.8)               | 55 (1397.0)  | 116 (2946.4) |
| 2000       | 9270 (4205)     | 250 (946)               | 87 (2209.8)               | 59 (1498.6)  | 118 (2997.2) |
| 2500       | 10,510 (4767)   | 270 (1022)              | 87 (2209.8)               | 61 (1549.4)  | 119 (3022.6) |
| 3000       | 12,100 (5488)   | 310 (1173)              | 87 (2209.8)               | 65 (1651.0)  | 119 (3022.6) |
| 3750       | 14,380 (6523)   | 390 (1476)              | 87 (2209.8)               | 65 (1651.0)  | 121 (3073.4) |
| 5000       | 18,490 (8387)   | 560 (2120)              | 97 (2463.8)               | 68 (1727.2)  | 122 (3098.8) |
| 7500       | 32,180 (14,597) | 1020 (3861)             | 98 (2489.2)               | 112 (2844.8) | 131 (3327.4) |
| 10,000     | 46,580 (21,128) | 1760 (6662)             | 119 (3022.6)              | 120 (3048.0) | 131 (3327.4) |

**Table 13.0-14. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 13800D, 95 BIL  
LV 4160Y, 60 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 5340 (2422)     | 180 (681)               | 87 (2209.8)               | 49 (1244.6)  | 79 (2006.6)  |
| 1000       | 6120 (2776)     | 190 (719)               | 87 (2209.8)               | 51 (1295.4)  | 82 (2082.8)  |
| 1500       | 7660 (3475)     | 220 (833)               | 87 (2209.8)               | 56 (1422.4)  | 116 (2946.4) |
| 2000       | 9080 (4119)     | 250 (946)               | 87 (2209.8)               | 59 (1498.6)  | 118 (2997.2) |
| 2500       | 11,180 (5071)   | 290 (1098)              | 87 (2209.8)               | 64 (1625.6)  | 119 (3022.6) |
| 3000       | 12,470 (5656)   | 310 (1173)              | 87 (2209.8)               | 66 (1676.4)  | 115 (2921.0) |
| 3750       | 14,590 (6618)   | 360 (1363)              | 87 (2209.8)               | 68 (1727.2)  | 121 (3073.4) |
| 5000       | 18,330 (8314)   | 540 (2044)              | 93 (2362.2)               | 68 (1727.2)  | 122 (3098.8) |
| 7500       | 31,330 (14,211) | 970 (3672)              | 98 (2489.2)               | 111 (2819.4) | 131 (3327.4) |
| 10,000     | 39,050 (17,713) | 1230 (4656)             | 101 (2565.4)              | 114 (2895.6) | 131 (3327.4) |



### Layout Dimensions

For special 55 °C rise units, bus duct throats and air terminal chambers, see **Notes 2 through 6** at bottom of page for dimensions that should be added to the table dimensions.

**Table 13.0-15. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 22900D, 150 BIL  
LV 2400Y, 45 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 5970 (2708)     | 230 (871)               | 87 (2209.8)               | 52 (1320.8)  | 73 (1854.2)  |
| 1000       | 6820 (3093)     | 240 (908)               | 87 (2209.8)               | 54 (1371.6)  | 91 (2311.4)  |
| 1500       | 8710 (3951)     | 280 (1060)              | 87 (2209.8)               | 57 (1447.8)  | 95 (2413.0)  |
| 2000       | 10,140 (4599)   | 310 (1173)              | 87 (2209.8)               | 58 (1473.2)  | 110 (2794.0) |
| 2500       | 11,890 (5393)   | 338 (1279)              | 87 (2209.8)               | 62 (1574.8)  | 121 (3073.4) |
| 3000       | 13,480 (6114)   | 380 (1438)              | 87 (2209.8)               | 66 (1676.4)  | 124 (3149.6) |
| 3750       | 15,820 (7176)   | 440 (1666)              | 87 (2209.8)               | 68 (1727.2)  | 125 (3175.0) |
| 5000       | 19,250 (8732)   | 540 (2044)              | 87 (2209.8)               | 70 (1778.0)  | 129 (3276.6) |
| 7500       | 32,700 (14,832) | 1090 (4126)             | 100 (2540.0)              | 99 (2514.6)  | 133 (3378.2) |
| 10,000     | 50,160 (22,752) | 2200 (8328)             | 120 (3048.0)              | 118 (2997.2) | 133 (3378.2) |

**Table 13.0-16. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 22900D, 150 BIL  
LV 4160Y, 60 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 6090 (2762)     | 230 (871)               | 87 (2209.8)               | 52 (1320.8)  | 75 (1905.0)  |
| 1000       | 7110 (3225)     | 250 (946)               | 87 (2209.8)               | 55 (1397.0)  | 91 (2311.4)  |
| 1500       | 8630 (3918)     | 280 (1060)              | 87 (2209.8)               | 56 (1422.4)  | 102 (2590.8) |
| 2000       | 10,050 (4559)   | 310 (1173)              | 87 (2209.8)               | 58 (1473.2)  | 107 (2717.8) |
| 2500       | 12,170 (5520)   | 350 (1325)              | 87 (2209.8)               | 63 (1600.2)  | 114 (2895.6) |
| 3000       | 13,600 (6169)   | 380 (1438)              | 87 (2209.8)               | 66 (1676.4)  | 116 (2946.4) |
| 3750       | 15,300 (6940)   | 420 (1590)              | 87 (2209.8)               | 68 (1727.2)  | 126 (3200.4) |
| 5000       | 19,350 (8777)   | 580 (2196)              | 89 (2260.6)               | 70 (1778.0)  | 129 (3276.6) |
| 7500       | 32,590 (14,783) | 1040 (3937)             | 94 (2387.6)               | 98 (2489.2)  | 134 (3403.6) |
| 10,000     | 40,250 (18,257) | 1370 (5186)             | 109 (2768.6)              | 102 (2590.8) | 137 (3479.8) |

**Table 13.0-17. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 22900D, 150 BIL  
LV 12470Y, 95 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |             |              |
|------------|-----------------|-------------------------|---------------------------|-------------|--------------|
|            |                 |                         | Height                    | Width       | Depth        |
| 750        | 6930 (3143)     | 360 (1363)              | 87 (2209.8)               | 56 (1422.4) | 66 (1676.4)  |
| 1000       | 7920 (3592)     | 300 (1136)              | 87 (2209.8)               | 58 (1473.2) | 72 (1828.8)  |
| 1500       | 9370 (4250)     | 310 (1173)              | 87 (2209.8)               | 59 (1498.6) | 90 (2286.0)  |
| 2000       | 11,240 (5098)   | 330 (1249)              | 87 (2209.8)               | 62 (1574.8) | 104 (2641.6) |
| 2500       | 12,760 (5788)   | 370 (1401)              | 87 (2209.8)               | 66 (1676.4) | 110 (2794.0) |
| 3000       | 14,260 (6468)   | 390 (1476)              | 87 (2209.8)               | 69 (1752.6) | 111 (2819.4) |
| 3750       | 15,910 (7217)   | 420 (1590)              | 87 (2209.8)               | 69 (1752.6) | 122 (3098.8) |
| 5000       | 19,830 (8995)   | 530 (2006)              | 89 (2209.8)               | 71 (1803.4) | 130 (3302.0) |
| 7500       | 33,990 (15,418) | 1100 (4164)             | 94 (2387.6)               | 97 (2463.8) | 139 (3530.6) |
| 10,000     | 39,610 (17,967) | 1280 (4845)             | 109 (2768.6)              | 99 (2514.6) | 139 (3530.6) |

- Notes:**
1. Dimensions are APPROXIMATE. NOT FOR CONSTRUCTION.
  2. For 55 °C units, add 5.00 inches (127.0 mm) to width dimension and 10 in (254.0 mm) to depth dimension.
  3. Add 9.00 inches (228.6 mm) to width dimension for each bus duct throat.
  4. Add 22.00 inches (558.8 mm) to width dimension for each 15 kV air terminal chamber.
  5. Add 25.00 inches (635.0 mm) to width dimension for each 27 kV air terminal chamber.
  6. Add 35.00 inches (889.0 mm) to width dimension for each 34.5 kV air terminal chamber.

**Table 13.0-18. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 34400D, 200 BIL  
LV 2400Y, 45 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 7600 (3447)     | 370 (1401)              | 107 (2717.8)              | 60 (1524.0)  | 68 (1727.2)  |
| 1000       | 8460 (3837)     | 390 (1476)              | 107 (2717.8)              | 60 (1524.0)  | 84 (2133.6)  |
| 1500       | 10,740 (4872)   | 420 (1590)              | 107 (2717.8)              | 62 (1574.8)  | 107 (2717.8) |
| 2000       | 12,260 (5561)   | 460 (1741)              | 107 (2717.8)              | 64 (1625.6)  | 115 (2921.0) |
| 2500       | 13,760 (6241)   | 490 (1855)              | 107 (2717.8)              | 64 (1625.6)  | 121 (3073.4) |
| 3000       | 15,020 (6813)   | 520 (1968)              | 107 (2717.8)              | 66 (1676.4)  | 121 (3073.4) |
| 3750       | 16,950 (7688)   | 570 (2158)              | 107 (2717.8)              | 78 (1981.2)  | 129 (3276.6) |
| 5000       | 20,270 (9194)   | 650 (2461)              | 109 (2768.6)              | 92 (2336.8)  | 132 (3352.8) |
| 7500       | 33,980 (15,413) | 1200 (4542)             | 120 (3048.0)              | 117 (2971.8) | 136 (3454.4) |
| 10,000     | 42,340 (19,205) | 1440 (5451)             | 129 (3276.6)              | 150 (3810.0) | 136 (3454.4) |

**Table 13.0-19. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 34400D, 200 BIL  
LV 4160Y, 60 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 7930 (3597)     | 380 (1438)              | 107 (2717.8)              | 61 (1549.4)  | 68 (1727.2)  |
| 1000       | 8840 (4010)     | 400 (1514)              | 107 (2717.8)              | 61 (1549.4)  | 81 (2057.4)  |
| 1500       | 10,710 (4858)   | 440 (1666)              | 107 (2717.8)              | 62 (1574.8)  | 95 (2413.0)  |
| 2000       | 12,530 (5684)   | 470 (1779)              | 107 (2717.8)              | 64 (1625.6)  | 117 (2971.8) |
| 2500       | 13,920 (6314)   | 500 (1893)              | 107 (2717.8)              | 66 (1676.4)  | 117 (2971.8) |
| 3000       | 15,620 (7085)   | 560 (2120)              | 107 (2717.8)              | 69 (1752.6)  | 127 (3225.8) |
| 3750       | 17,580 (7974)   | 610 (2309)              | 107 (2717.8)              | 71 (1803.4)  | 127 (3225.8) |
| 5000       | 20,980 (9516)   | 680 (2574)              | 108 (2743.2)              | 84 (2133.6)  | 132 (3352.8) |
| 7500       | 32,460 (14,724) | 1080 (4088)             | 119 (3022.6)              | 116 (2946.4) | 135 (3429.0) |
| 10,000     | 40,320 (18,289) | 1360 (5148)             | 129 (3276.6)              | 119 (3022.6) | 135 (3429.0) |

**Table 13.0-20. 65 °C Rise,  
Silicone/Environmentally Friendly Fluid  
HV 34400D, 200 BIL  
LV 13800Y, 95 BIL**

| kVA Rating | Weight Lbs (kg) | Gallons (Liters) Liquid | Dimensions in Inches (mm) |              |              |
|------------|-----------------|-------------------------|---------------------------|--------------|--------------|
|            |                 |                         | Height                    | Width        | Depth        |
| 750        | 9270 (4205)     | 400 (1514)              | 107 (2717.8)              | 65 (1651.0)  | 55 (1397.0)  |
| 1000       | 9900 (4491)     | 420 (1590)              | 107 (2717.8)              | 65 (1651.0)  | 67 (1701.8)  |
| 1500       | 11,620 (5271)   | 460 (1741)              | 107 (2717.8)              | 65 (1651.0)  | 96 (2438.4)  |
| 2000       | 13,160 (5969)   | 500 (1893)              | 107 (2717.8)              | 65 (1651.0)  | 117 (2971.8) |
| 2500       | 14,580 (6613)   | 530 (2006)              | 107 (2717.8)              | 67 (1701.8)  | 117 (2971.8) |
| 3000       | 16,090 (7298)   | 560 (2120)              | 107 (2717.8)              | 69 (1752.6)  | 123 (3124.2) |
| 3750       | 17,930 (8111)   | 600 (2271)              | 108 (2743.2)              | 77 (1955.8)  | 130 (3302.0) |
| 5000       | 21,410 (9720)   | 680 (2574)              | 110 (2794.0)              | 77 (1955.8)  | 131 (3327.4) |
| 7500       | 32,060 (14,542) | 1010 (3823)             | 114 (2895.6)              | 116 (2946.4) | 132 (3352.8) |
| 10,000     | 41,850 (18,983) | 1330 (5035)             | 122 (3098.8)              | 148 (3759.2) | 116 (2946.4) |



## General Description

## General Description

## Dry-Type Transformers

- Indoor/outdoor applications
- No fire risk
- No need for containment or fire suppression
- Low maintenance
- Easy transit/installation
- Close-coupled with switchgear/switchboard
- Primary voltage: 6.9–69 kV
- Transformer kVA: 500–20,000 kVA
- Secondary voltage: 2.4–34.5 kV

## VPI

- Aluminum windings—copper optional
- Step-lap mitered core
- 220 °C insulation system—150 °C average temperature rise
- Vacuum pressure impregnated in polyester resin
- Four full-capacity taps on HV winding rated 2-1/2% 2-FCAN—2-FCBN on units with voltage above 601 V
- NEMA 1 heavy-gauge ventilated enclosure with removable panels front and rear
- ANSI 61 gray paint electrostatically applied using dry powder
- Vibration isolation pads between core and coil and enclosure
- Base equipped with jacking pads and designed for rolling or skidding enclosure in any direction
- Provisions for lifting core and coil assembly
- Diagrammatic aluminum nameplate
- 100% QC impulse test
- Short-circuit design verification



Dry-Type Unit Substation Transformer

## Cast Coil


- Windings cast in a mold. HV coils vacuum cast in epoxy in a metal mold. LV coils encapsulated/pressure-injected in epoxy for 600 V and below
- Aluminum windings—copper optional
- Step-lap mitered core
- 180 °C insulation system—115 °C average temperature rise
- Four full-capacity taps on HV winding rated 2-1/2% 2-FCAN—2-FCBN on units with voltage above 601 V
- NEMA 1 heavy-gauge ventilated enclosure with removable panels front and rear
- ANSI 61 gray paint electrostatically applied using dry powder
- Vibration isolation pads between core and coil and enclosure
- Base equipped with jacking pads and designed for rolling or skidding enclosure in any direction
- Provisions for lifting core and coil assembly
- Diagrammatic aluminum nameplate
- 100% QC impulse test
- Partial discharge-free (less than 10 pc at 150% rated voltage)

## RESIBLOC

- High voltage windings cast in epoxy reinforced by fiberglass rovings
- Copper high voltage, aluminum low voltage windings
- Step-lap mitered core
- 155 °C insulation system—80 °C average temperature rise
- Four full-capacity taps on HV winding rated 2-1/2% 2-FCAN—2-FCBN on units with voltage above 601 V
- NEMA 1 heavy-gauge ventilated enclosure with removable panels front and rear
- ANSI 61 gray paint electrostatically applied using dry powder
- Vibration isolation pads between core and coil and enclosure
- Base equipped with jacking pads and designed for rolling or skidding enclosure in any direction
- Provisions for lifting core and coil assembly
- Diagrammatic aluminum nameplate
- 100% QC impulse test
- Partial discharge-free (less than 10 pc at 150% rated voltage)

## Layout Dimensions

### Layout Dimensions



**Figure 13.0-4. Indoor VPI/VPE/Cast/RESIBLOC Primary Unit Substations—Plan View**

① Optional transition section is not required for most dry-type transformers. They may only be required for connection to existing transformers or for rear alignment. Contact Eaton for additional details.

**Table 13.0-21. Indoor Dimension References**

| Equipment   | Dimensions     | Reference                             |
|-------------|----------------|---------------------------------------|
| Transformer | W, D           | Page 13.0-12                          |
| MVC         | Ws, Ds         | Tab 10, Pages 10.1-25 through 10.1-41 |
| MVS         | Wp, Dp, Ws, Ds | Tab 8, Pages 8.0-18 through 8.0-28    |
| ME          | Wp, Dp, Ws, Ds | Tab 7, Pages 7.1-4 through 7.1-6      |
| MC          | Wp, Dp, Ws, Ds | Tab 5, Pages 5.5-1 through 5.5-41     |

**Transition Section Dimensions in Inches (mm)**

| Primary or Secondary Equipment | W1   |       |       |       |
|--------------------------------|------|-------|-------|-------|
|                                | 5 kV | 15 kV | 27 kV | 38 kV |
| MVC ①②                         | 75   | —     | —     | —     |
| MVS                            | 0    | 0     | 30    | 30    |
| ME                             | 20   | 20    | 30    | 30    |
| MC                             | 18   | 18    | 36    | 42    |

① Front to rear centerline aligns with centerline of the transformer.

② Four-wire connections are not available with MVC equipment.

**Note:** Surge arresters as discussed in **Tabs 7** and **8** can be located in the primary of dry-type transformers.

**Note:** Dimensions are APPROXIMATE.


#### Legend:

MVC = Medium Voltage Motor Control, Type AMPGARD  
MVS = Medium Voltage Metal-Enclosed Switches, Type MVS  
ME = Medium Voltage Metal-Enclosed Breakers, Type MEB, MEF, MSB  
MC = Medium Voltage Metal-Clad Breaker Assemblies, Type VacClad-W

## Layout Dimensions

**Substation with Air Terminal Chamber (ATC) Utilization Dry-Type Transformer**

A substation using one or two air terminal chambers (ATCs) is different from a substation using close-coupling on both the primary and secondary sides. An ATC uses a cable connection on either the primary side, secondary side or both, and is placed between the transformer and the remotely mounted primary or secondary equipment.



**Figure 13.0-5. Dry-Type Indoor Using Air Terminal Chambers—Top View**

① Transformer dimensions are shown on the following page in **Table 13.0-23**.

② ATC depths shall match transformer depth, for any kVA of interest. See **Table 13.0-23**.

**Table 13.0-22. Primary or Secondary ATC or Transition Section—Dimensions in Inches (mm)**

| Voltage | Three-Phase, Three-Wire or<br>Three-Phase, Four-Wire |                |                 |
|---------|------------------------------------------------------|----------------|-----------------|
|         | ATC Widths                                           |                | ATC Depths      |
| kV      | W <sub>1</sub>                                       | W <sub>2</sub> | D               |
| 5 or 15 | 18.00 (457.2)                                        | 18.00 (457.2)  | D <sub>TX</sub> |
| 27      | 30.00 (762.0)                                        | 30.00 (762.0)  | D <sub>TX</sub> |
| 38      | 36.00 (914.4)                                        | 36.00 (914.4)  | D <sub>TX</sub> |

**Note:** Typical ATC widths by kV are listed in the table above. The width of any ATC can be expanded to allow for the installation of additional conduits. When calculating the area of the conduit opening, allow for a 3.00-inch (76.2 mm) lip around the entire perimeter of the ATC.

## Layout Dimensions

**Table 13.0-23. VPI/VPE/Cast/RESIBLOC Ventilated Dry-Type—Dimensions in Inches (mm)**

Aluminum Windings, Standard Design and Losses, Delta-Wye

VPI/VPE = 150 °C Rise, Cast/RESIBLOC = 80 °C Rise


| kVA             | HV (kV) | HV BIL | Height       | Width        | Depth       | Weight in Lbs (kg) |                 |
|-----------------|---------|--------|--------------|--------------|-------------|--------------------|-----------------|
|                 |         |        |              |              |             | VPI/VPE            | Cast/RESIBLOC   |
| 5 kV Secondary  |         |        |              |              |             |                    |                 |
| 2000            | 15      | 95     | 102 (2590.8) | 120 (3048.0) | 68 (1727.2) | 11,000 (4994)      | 14,000 (6356)   |
|                 | 27      | 125    | 112 (2844.8) | 130 (3302.0) | 72 (1828.8) | 13,000 (5902)      | 16,000 (7264)   |
|                 | 38      | 150    | 130 (3302.0) | 148 (3759.2) | 78 (1981.2) | 13,500 (6129)      | 18,000 (8172)   |
| 2500            | 15      | 95     | 112 (2844.8) | 124 (3149.6) | 68 (1727.2) | 13,500 (6129)      | 17,000 (7718)   |
|                 | 27      | 125    | 130 (3302.0) | 140 (3556.0) | 78 (1981.2) | 15,000 (6810)      | 19,000 (8626)   |
|                 | 38      | 150    | 138 (3505.2) | 150 (3810.0) | 78 (1981.2) | 15,500 (7037)      | 21,000 (9534)   |
| 3000            | 15      | 95     | 120 (3048.0) | 130 (3302.0) | 72 (1828.8) | 16,500 (7491)      | 22,000 (9988)   |
|                 | 27      | 125    | 130 (3302.0) | 140 (3556.0) | 78 (1981.2) | 18,500 (8399)      | 24,000 (10,896) |
|                 | 38      | 150    | 138 (3505.2) | 150 (3810.0) | 78 (1981.2) | 19,500 (8853)      | 26,000 (11,804) |
| 5000            | 15      | 95     | 130 (3302.0) | 140 (3556.0) | 78 (1981.2) | 22,000 (9988)      | 31,000 (14,074) |
|                 | 27      | 125    | 138 (3505.2) | 148 (3759.2) | 78 (1981.2) | 23,000 (10,442)    | 33,000 (14,982) |
|                 | 38      | 150    | 140 (3556.0) | 150 (3810.0) | 82 (2082.8) | 24,000 (10,896)    | 35,000 (15,890) |
| 7500            | 15      | 95     | 140 (3556.0) | 150 (3810.0) | 78 (1981.2) | 24,500 (11,123)    | 48,000 (21,792) |
|                 | 27      | 125    | 140 (3556.0) | 150 (3810.0) | 84 (2133.6) | 26,000 (11,804)    | 50,000 (22,700) |
|                 | 38      | 150    | 140 (3556.0) | 154 (3911.6) | 88 (2235.2) | 27,000 (12,258)    | 52,000 (23,608) |
| 10000           | 15      | 95     | 140 (3556.0) | 160 (4064.0) | 78 (1981.2) | 29,000 (13,166)    | 62,000 (28,148) |
|                 | 27      | 125    | 140 (3556.0) | 160 (4064.0) | 84 (2133.6) | 30,000 (13,620)    | 64,000 (29,056) |
|                 | 38      | 150    | 148 (3759.2) | 160 (4064.0) | 90 (2286.0) | 31,000 (14,074)    | 66,000 (29,964) |
| 15 kV Secondary |         |        |              |              |             |                    |                 |
| 2000            | 27      | 125    | 102 (2590.8) | 120 (3048.0) | 72 (1828.8) | 12,000 (5448)      | 18,000 (8172)   |
|                 | 38      | 150    | 112 (2844.8) | 130 (3302.0) | 72 (1828.8) | 13,500 (6129)      | 20,000 (9080)   |
| 2500            | 27      | 125    | 112 (2844.8) | 140 (3556.0) | 78 (1981.2) | 14,000 (6356)      | 21,000 (9534)   |
|                 | 38      | 150    | 120 (3048.0) | 140 (3556.0) | 78 (1981.2) | 14,500 (6583)      | 23,000 (10,442) |
| 3000            | 27      | 125    | 120 (3048.0) | 148 (3759.2) | 78 (1981.2) | 15,500 (7037)      | 26,000 (11,804) |
|                 | 38      | 150    | 124 (3149.6) | 150 (3810.0) | 82 (2082.8) | 16,000 (7264)      | 28,000 (12,712) |
| 5000            | 27      | 125    | 124 (3149.6) | 150 (3810.0) | 88 (2235.2) | 17,500 (7945)      | 35,000 (15,890) |
|                 | 38      | 150    | 130 (3302.0) | 154 (3911.6) | 88 (2235.2) | 19,000 (8626)      | 37,000 (16,798) |
| 7500            | 27      | 125    | 140 (3556.0) | 154 (3911.6) | 88 (2235.2) | 20,500 (9307)      | 52,000 (23,608) |
|                 | 38      | 150    | 140 (3556.0) | 160 (4064.0) | 90 (2286.0) | 22,500 (10,215)    | 54,000 (24,516) |
| 10000           | 27      | 125    | 148 (3759.2) | 160 (4064.0) | 90 (2286.0) | 23,500 (10,669)    | 66,000 (29,964) |
|                 | 38      | 150    | 148 (3759.2) | 160 (4064.0) | 90 (2286.0) | 25,000 (11,350)    | 68,000 (30,872) |

- Notes:** 1. Add 18.00 inches (457.2 mm) to width dimension for each 15 kV air terminal chamber.  
2. Add 30.00 inches (762.0 mm) to width dimension for each 25 kV air terminal chamber.  
3. Add 36.00 inches (914.4 mm) to width dimension for each 38 kV air terminal chamber.  
4. Add 6.00 inches (152.4 mm) to depth dimension for seismic rating <1.25 SDS.  
5. Add 12.00 inches (304.8 mm) to depth dimension for seismic rating ≥1.25 SDS.  
6. Dimensions are APPROXIMATE. NOT FOR CONSTRUCTION.

## Technical Data

**ANSI Segment Identification  
for HV and LV Bushings/  
Terminations on Dry and  
Liquid Transformers**

The plan view below shows the ANSI segments used to identify the location of both the HV and LV bushings.



**Figure 13.0-6. Front (Nameplate, Gauges, etc.)**

**HV:** Segment 2 is standard for wall-mounted bushings (optional Segment 4)

Segment 3 is standard for cover-mounted bushings

**LV:** Segment 4 wall-mounted is standard (optional Segment 2)

**Note:** See **Tab 9** for fuse selections.

**Table 13.0-24. Dry-Type Transformer Rating Table—112 to 10,000 kVA**

| Primary/Secondary   |                      |
|---------------------|----------------------|
| BIL kV <sup>①</sup> | Maximum Voltage (kV) |
| 20/30/45            | 2.5                  |
| 30/45/60/75/95      | 5.0                  |
| 45/60/75/95         | 8.7                  |
| 60/75/95/110/125    | 15.0                 |
| 110/125             | 25.0                 |
| 125                 | 27.0                 |
| 150                 | 34.5                 |

<sup>①</sup> First BIL rating given below is standard. Others shown are optional.

**Table 13.0-25. Liquid Transformer Rating Table—500 to 10,000 kVA**

| Primary             |                                | Secondary |                                                                |
|---------------------|--------------------------------|-----------|----------------------------------------------------------------|
| BIL kV <sup>②</sup> | Voltage Range                  | BIL kV    | Voltage Range                                                  |
| 95/110              | 12000D, 12470D, 13200D, 13800D | 45        | 2400Y, 2400D, 2520D                                            |
| 95/110              | 12000D, 12470D, 13200D, 13800D | 60        | 4160Y, 4160D, 4360Y, 4800D, 5040D                              |
| 125/150             | 22900D                         | 45        | 2400Y, 2400D, 2520D                                            |
| 125/150             | 22900D                         | 60        | 4160Y, 4160D, 4360Y, 4800D                                     |
| 125/150             | 22900D                         | 75        | 6900D, 7200D, 7560D, 8320D, 8720D                              |
| 125/150             | 22900D                         | 95        | 12000D, 12470Y, 12600D, 13090Y, 13200Y, 13200D, 13800Y, 14400D |
| 150/200             | 34400D, 34500D                 | 45        | 2400Y, 2400D, 2520D                                            |
| 150/200             | 34400D, 34500D                 | 60        | 4160Y, 4160D, 4360Y, 4800D, 5040D                              |
| 150/200             | 34400D, 34500D                 | 75        | 6900D, 7200D, 7560D 8320Y, 8720D                               |
| 150/200             | 34400D, 34500D                 | 95        | 12000D, 12470Y, 12600D, 13090Y, 13200Y, 13200D, 13800Y, 14400D |
| 250                 | 46000                          |           |                                                                |
| 350                 | 69000                          |           |                                                                |

<sup>②</sup> First BIL rating given below is standard. Others shown are optional.

Transformers will have a minimum 98% efficiency for all ratings (maximum 2% losses).

**Table 13.0-26. Standard Sound Levels—Decibels (per ANSI TR-1)**

| kVA   | Liquid-Filled Transformers |    | Vent Dry-Type and Cast Coil Transformers |    |
|-------|----------------------------|----|------------------------------------------|----|
|       | OA                         | FA | AA                                       | FA |
| 500   | 56                         | 67 | 60                                       | 67 |
| 750   | 58                         | 67 | 64                                       | 67 |
| 1000  | 58                         | 67 | 64                                       | 67 |
| 1500  | 60                         | 67 | 65                                       | 68 |
| 2000  | 61                         | 67 | 66                                       | 69 |
| 2500  | 62                         | 67 | 68                                       | 71 |
| 3000  | 63                         | 67 | 68                                       | 71 |
| 3750  | 64                         | 67 | 70                                       | 73 |
| 5000  | 65                         | 67 | 71                                       | 73 |
| 6000  | 66                         | 68 | 72                                       | 74 |
| 7500  | 67                         | 69 | 73                                       | 75 |
| 10000 | 68                         | 70 | —                                        | 76 |

**Table 13.0-27. Standard Impedances (Percent)**

| HV kV BIL Class | Low Voltage Below 2400 V | Low Voltage 2400 V and Above |
|-----------------|--------------------------|------------------------------|
| 45–150          | 5.75 <sup>③</sup>        | 6.50 <sup>④</sup>            |
| 200             | 7.25                     | 7.00                         |
| 250             | 7.75                     | 7.50                         |
| 350             | —                        | 8.00                         |

<sup>③</sup> 6.75% is also available as an option.

<sup>④</sup> 5.50% is also available as an option.

## Technical Data

**Table 13.0-28. Liquid Filled 15 kV Primary 55 °C Temp. Rise**

| kVA    | No Load at 75 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 75 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 95 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1795                                | 10,085                                              | 11,880                                      | 4320                                                                                                  |
| 1000   | 2277                                | 12,741                                              | 15,018                                      | 5460                                                                                                  |
| 1500   | 3193                                | 17,352                                              | 20,545                                      | 7530                                                                                                  |
| 2000   | 4045                                | 21,031                                              | 25,076                                      | 9300                                                                                                  |
| 2500   | 4833                                | 23,776                                              | 28,609                                      | 10,780                                                                                                |
| 3000   | 5364                                | 23,823                                              | 29,187                                      | 11,320                                                                                                |
| 3750   | 6424                                | 28,273                                              | 34,697                                      | 13,490                                                                                                |
| 5000   | 8152                                | 35,345                                              | 43,497                                      | 16,990                                                                                                |
| 7500   | 11,458                              | 48,205                                              | 59,663                                      | 23,510                                                                                                |
| 10,000 | 14,565                              | 59,352                                              | 73,917                                      | 29,400                                                                                                |

**Table 13.0-29. Liquid Filled 5 kV Primary 55 °C Temp. Rise**

| kVA    | No Load at 75 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 75 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 60 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1777                                | 9984                                                | 11,761                                      | 4270                                                                                                  |
| 1000   | 2254                                | 12,613                                              | 14,867                                      | 5410                                                                                                  |
| 1500   | 3161                                | 17,178                                              | 20,339                                      | 7460                                                                                                  |
| 2000   | 4004                                | 20,820                                              | 24,824                                      | 9210                                                                                                  |
| 2500   | 4784                                | 23,538                                              | 28,322                                      | 10,670                                                                                                |
| 3000   | 4310                                | 23,584                                              | 27,894                                      | 10,210                                                                                                |
| 3750   | 6359                                | 27,990                                              | 34,349                                      | 13,360                                                                                                |
| 5000   | 8070                                | 34,991                                              | 43,061                                      | 16,820                                                                                                |
| 7500   | 11,343                              | 47,722                                              | 59,065                                      | 23,270                                                                                                |
| 10,000 | 14,419                              | 58,758                                              | 73,177                                      | 29,110                                                                                                |

**Table 13.0-30. Liquid Filled 25 kV Primary 55 °C Temp. Rise**

| kVA    | No Load at 75 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 75 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 150 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|--------------------------------------------------------------------------------------------------------|
| 750    | 1812                                | 10,183                                              | 11,995                                      | 4360                                                                                                   |
| 1000   | 2299                                | 12,865                                              | 15,164                                      | 5520                                                                                                   |
| 1500   | 3224                                | 17,521                                              | 20,745                                      | 7600                                                                                                   |
| 2000   | 4084                                | 21,236                                              | 25,320                                      | 9390                                                                                                   |
| 2500   | 4879                                | 24,008                                              | 28,887                                      | 10,880                                                                                                 |
| 3000   | 4396                                | 24,055                                              | 28,451                                      | 10,410                                                                                                 |
| 3750   | 6486                                | 28,549                                              | 35,035                                      | 13,620                                                                                                 |
| 5000   | 8231                                | 35,690                                              | 43,921                                      | 17,150                                                                                                 |
| 7500   | 11,569                              | 48,676                                              | 60,245                                      | 23,740                                                                                                 |
| 10,000 | 14,707                              | 59,933                                              | 74,640                                      | 29,690                                                                                                 |

**Table 13.0-31. Liquid Filled 35 kV Primary 55 °C Temp. Rise**

| kVA    | No Load at 75 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 75 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 200 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|--------------------------------------------------------------------------------------------------------|
| 750    | 1902                                | 10,692                                              | 12,594                                      | 4580                                                                                                   |
| 1000   | 2413                                | 13,508                                              | 15,921                                      | 5790                                                                                                   |
| 1500   | 3385                                | 18,397                                              | 21,782                                      | 7980                                                                                                   |
| 2000   | 4288                                | 22,298                                              | 26,586                                      | 9860                                                                                                   |
| 2500   | 5122                                | 25,208                                              | 30,330                                      | 11,420                                                                                                 |
| 3000   | 4615                                | 25,257                                              | 29,872                                      | 10,930                                                                                                 |
| 3750   | 6810                                | 29,976                                              | 36,786                                      | 14,300                                                                                                 |
| 5000   | 8642                                | 37,474                                              | 46,116                                      | 18,010                                                                                                 |
| 7500   | 12,147                              | 51,109                                              | 63,256                                      | 24,920                                                                                                 |
| 10,000 | 15,442                              | 62,929                                              | 78,371                                      | 31,170                                                                                                 |

**Table 13.0-32. Liquid Filled 15 kV Primary 65 °C Temp. Rise**

| kVA    | No Load at 85 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 85 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 95 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1947                                | 10,942                                              | 12,889                                      | 4680                                                                                                  |
| 1000   | 2470                                | 13,823                                              | 16,293                                      | 5930                                                                                                  |
| 1500   | 3464                                | 18,826                                              | 22,290                                      | 8170                                                                                                  |
| 2000   | 4388                                | 22,818                                              | 27,206                                      | 10,090                                                                                                |
| 2500   | 5243                                | 25,796                                              | 31,039                                      | 11,690                                                                                                |
| 3000   | 5819                                | 25,847                                              | 31,666                                      | 12,280                                                                                                |
| 3750   | 6970                                | 30,676                                              | 37,646                                      | 14,640                                                                                                |
| 5000   | 8844                                | 38,349                                              | 47,193                                      | 18,430                                                                                                |
| 7500   | 12,431                              | 52,302                                              | 64,733                                      | 25,510                                                                                                |
| 10,000 | 15,803                              | 64,396                                              | 80,199                                      | 31,900                                                                                                |

**Table 13.0-33. Liquid Filled 5 kV Primary 65 °C Temp. Rise**

| kVA    | No Load at 85 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 85 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 60 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1928                                | 10,832                                              | 12,760                                      | 4640                                                                                                  |
| 1000   | 2445                                | 13,685                                              | 16,130                                      | 5870                                                                                                  |
| 1500   | 3429                                | 18,638                                              | 22,067                                      | 8090                                                                                                  |
| 2000   | 4344                                | 22,589                                              | 26,933                                      | 9990                                                                                                  |
| 2500   | 5190                                | 25,538                                              | 30,728                                      | 11,570                                                                                                |
| 3000   | 4676                                | 25,584                                              | 30,260                                      | 11,070                                                                                                |
| 3750   | 6899                                | 30,369                                              | 37,268                                      | 14,490                                                                                                |
| 5000   | 8755                                | 37,965                                              | 46,720                                      | 18,250                                                                                                |
| 7500   | 12,307                              | 51,778                                              | 64,085                                      | 25,250                                                                                                |
| 10,000 | 15,644                              | 63,752                                              | 79,396                                      | 31,580                                                                                                |

**Table 13.0-34. Liquid Filled 25 kV Primary 65 °C Temp. Rise**

| kVA    | No Load at 85 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 85 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 150 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|--------------------------------------------------------------------------------------------------------|
| 750    | 1966                                | 11,048                                              | 13,014                                      | 4730                                                                                                   |
| 1000   | 2494                                | 13,958                                              | 16,452                                      | 5980                                                                                                   |
| 1500   | 3498                                | 19,010                                              | 22,508                                      | 8250                                                                                                   |
| 2000   | 4431                                | 23,041                                              | 27,472                                      | 10,190                                                                                                 |
| 2500   | 5293                                | 26,048                                              | 31,341                                      | 11,810                                                                                                 |
| 3000   | 4769                                | 26,099                                              | 30,868                                      | 11,290                                                                                                 |
| 3750   | 7037                                | 30,875                                              | 37,912                                      | 14,760                                                                                                 |
| 5000   | 8930                                | 38,735                                              | 47,665                                      | 18,610                                                                                                 |
| 7500   | 12,552                              | 52,813                                              | 65,365                                      | 25,760                                                                                                 |
| 10,000 | 15,957                              | 65,027                                              | 80,984                                      | 32,210                                                                                                 |

**Table 13.0-35. Liquid Filled 35 kV Primary 65 °C Temp. Rise**

| kVA    | No Load at 85 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 85 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 200 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|--------------------------------------------------------------------------------------------------------|
| 750    | 2063                                | 11,600                                              | 13,663                                      | 4960                                                                                                   |
| 1000   | 2618                                | 14,656                                              | 17,274                                      | 6280                                                                                                   |
| 1500   | 3672                                | 19,960                                              | 23,632                                      | 8660                                                                                                   |
| 2000   | 4652                                | 24,193                                              | 28,845                                      | 10,700                                                                                                 |
| 2500   | 5557                                | 27,350                                              | 32,907                                      | 12,390                                                                                                 |
| 3000   | 5007                                | 27,403                                              | 32,410                                      | 11,860                                                                                                 |
| 3750   | 7388                                | 32,523                                              | 39,911                                      | 15,520                                                                                                 |
| 5000   | 9376                                | 40,659                                              | 50,035                                      | 19,540                                                                                                 |
| 7500   | 13,179                              | 55,453                                              | 68,632                                      | 27,040                                                                                                 |
| 10,000 | 16,754                              | 68,277                                              | 85,031                                      | 33,820                                                                                                 |

**Note:** Losses offered are typical only, not guaranteed. Losses based on aluminum windings. Losses based on LV rating 2-5 kV.



## Technical Data

Table 13.0-36. Biotemp Filled 15 kV Primary 55 °C Temp. Rise

| kVA    | No Load at 75 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 75 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 95 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1774                                | 9587                                                | 11,361                                      | 4170                                                                                                  |
| 1000   | 2258                                | 11,942                                              | 14,200                                      | 5240                                                                                                  |
| 1500   | 3188                                | 15,734                                              | 18,922                                      | 7120                                                                                                  |
| 2000   | 4069                                | 18,298                                              | 22,367                                      | 8640                                                                                                  |
| 2500   | 4900                                | 19,638                                              | 24,538                                      | 9810                                                                                                  |
| 3000   | 5299                                | 21,758                                              | 27,057                                      | 10,740                                                                                                |
| 3750   | 6350                                | 24,962                                              | 31,312                                      | 12,590                                                                                                |
| 5000   | 8085                                | 30,018                                              | 38,103                                      | 15,590                                                                                                |
| 7500   | 11,495                              | 39,066                                              | 50,561                                      | 21,260                                                                                                |
| 10,000 | 14,824                              | 46,694                                              | 61,518                                      | 26,500                                                                                                |

Table 13.0-37. Biotemp Filled 5 kV Primary 55 °C Temp. Rise

| kVA    | No load at 75 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 75 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 60 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1756                                | 9491                                                | 11,247                                      | 4130                                                                                                  |
| 1000   | 2235                                | 11,822                                              | 14,057                                      | 5190                                                                                                  |
| 1500   | 3156                                | 15,576                                              | 18,732                                      | 7050                                                                                                  |
| 2000   | 4028                                | 18,115                                              | 22,143                                      | 8560                                                                                                  |
| 2500   | 4851                                | 19,441                                              | 24,292                                      | 9710                                                                                                  |
| 3000   | 5246                                | 21,540                                              | 26,786                                      | 10,630                                                                                                |
| 3750   | 6286                                | 24,712                                              | 30,998                                      | 12,460                                                                                                |
| 5000   | 8004                                | 29,717                                              | 37,721                                      | 15,430                                                                                                |
| 7500   | 11,380                              | 38,675                                              | 50,055                                      | 21,050                                                                                                |
| 10,000 | 14,675                              | 46,227                                              | 60,902                                      | 26,230                                                                                                |

Table 13.0-38. Biotemp Filled 25 kV Primary 55 °C Temp. Rise

| kVA    | No Load at 75 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 75 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 150 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|--------------------------------------------------------------------------------------------------------|
| 750    | 1791                                | 9680                                                | 11,471                                      | 4210                                                                                                   |
| 1000   | 2279                                | 12,058                                              | 14,337                                      | 5290                                                                                                   |
| 1500   | 3219                                | 15,887                                              | 19,106                                      | 7190                                                                                                   |
| 2000   | 4108                                | 18,477                                              | 22,585                                      | 8730                                                                                                   |
| 2500   | 4948                                | 19,829                                              | 24,777                                      | 9910                                                                                                   |
| 3000   | 5350                                | 21,970                                              | 27,320                                      | 10,840                                                                                                 |
| 3750   | 6411                                | 25,206                                              | 31,617                                      | 12,710                                                                                                 |
| 5000   | 8164                                | 30,311                                              | 38,475                                      | 15,740                                                                                                 |
| 7500   | 11,607                              | 39,448                                              | 51,055                                      | 21,470                                                                                                 |
| 10,000 | 14,968                              | 47,150                                              | 62,118                                      | 26,760                                                                                                 |

Table 13.0-39. Biotemp Filled 35 kV Primary 55 °C Temp. Rise

| kVA    | No load at 75 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 75 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 200 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|--------------------------------------------------------------------------------------------------------|
| 750    | 1880                                | 10,164                                              | 12,044                                      | 4420                                                                                                   |
| 1000   | 2392                                | 12,660                                              | 15,052                                      | 5560                                                                                                   |
| 1500   | 3379                                | 16,681                                              | 20,060                                      | 7550                                                                                                   |
| 2000   | 4313                                | 19,400                                              | 23,713                                      | 9160                                                                                                   |
| 2500   | 5195                                | 20,820                                              | 26,015                                      | 10,400                                                                                                 |
| 3000   | 5617                                | 23,068                                              | 28,685                                      | 11,380                                                                                                 |
| 3750   | 6731                                | 26,466                                              | 33,197                                      | 13,350                                                                                                 |
| 5000   | 8572                                | 31,826                                              | 40,398                                      | 16,530                                                                                                 |
| 7500   | 12,187                              | 41,420                                              | 53,607                                      | 22,450                                                                                                 |
| 10,000 | 15,716                              | 49,507                                              | 65,223                                      | 28,090                                                                                                 |

Table 13.0-40. Biotemp Filled 15 kV Primary 65 °C Temp. Rise

| kVA    | No Load at 85 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 85 °C Ref. Temp. (Watts) | Total losses at 100% Load and 85 °C (Watts) | 95 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1924                                | 10,401                                              | 12,325                                      | 4520                                                                                                  |
| 1000   | 2449                                | 12,957                                              | 15,406                                      | 5690                                                                                                  |
| 1500   | 3458                                | 17,071                                              | 20,529                                      | 7730                                                                                                  |
| 2000   | 4414                                | 19,853                                              | 24,267                                      | 9380                                                                                                  |
| 2500   | 5316                                | 21,307                                              | 26,623                                      | 10,970                                                                                                |
| 3000   | 5749                                | 23,607                                              | 29,356                                      | 11,650                                                                                                |
| 3750   | 6889                                | 27,083                                              | 33,972                                      | 13,660                                                                                                |
| 5000   | 8772                                | 32,569                                              | 41,341                                      | 16,910                                                                                                |
| 7500   | 12,472                              | 42,386                                              | 54,858                                      | 23,070                                                                                                |
| 10,000 | 16,084                              | 50,662                                              | 66,746                                      | 28,750                                                                                                |

Table 13.0-41. Biotemp Filled 5 kV Primary 65 °C Temp. Rise

| kVA    | No Load at 85 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 85 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 60 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1905                                | 10,297                                              | 12,202                                      | 4480                                                                                                  |
| 1000   | 2424                                | 12,826                                              | 15,250                                      | 5630                                                                                                  |
| 1500   | 3424                                | 16,899                                              | 20,323                                      | 7650                                                                                                  |
| 2000   | 4370                                | 19,654                                              | 24,024                                      | 9280                                                                                                  |
| 2500   | 5263                                | 21,093                                              | 26,356                                      | 10,540                                                                                                |
| 3000   | 5691                                | 23,370                                              | 29,061                                      | 11,530                                                                                                |
| 3750   | 6820                                | 26,812                                              | 33,632                                      | 13,520                                                                                                |
| 5000   | 8684                                | 32,242                                              | 40,926                                      | 16,740                                                                                                |
| 7500   | 12,347                              | 41,962                                              | 54,309                                      | 22,840                                                                                                |
| 10,000 | 15,922                              | 50,156                                              | 66,078                                      | 28,460                                                                                                |

Table 13.0-42. Biotemp Filled 25 kV Primary °C Temp. Rise

| kVA    | No Load at 85 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 85 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 150 kV HV BIL Total Losses at 50% Load and 55 °C LL ref. temp and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------------------------------|
| 750    | 1943                                | 10,502                                              | 12,445                                      | 4570                                                                                                  |
| 1000   | 2472                                | 13,082                                              | 15,554                                      | 5740                                                                                                  |
| 1500   | 3492                                | 17,237                                              | 20,729                                      | 7800                                                                                                  |
| 2000   | 4457                                | 20,047                                              | 24,504                                      | 9470                                                                                                  |
| 2500   | 5368                                | 21,514                                              | 26,882                                      | 10,750                                                                                                |
| 3000   | 5804                                | 23,837                                              | 29,641                                      | 11,760                                                                                                |
| 3750   | 6955                                | 27,348                                              | 34,303                                      | 13,790                                                                                                |
| 5000   | 8857                                | 32,887                                              | 41,744                                      | 17,080                                                                                                |
| 7500   | 12,593                              | 42,801                                              | 55,394                                      | 23,290                                                                                                |
| 10,000 | 16,240                              | 51,157                                              | 67,397                                      | 29,030                                                                                                |

Table 13.0-43. Biotemp Filled 35 kV Primary 65 °C Temp. Rise

| kVA    | No Load at 85 °C Ref. Temp. (Watts) | Load Loss at 100% Load and 85 °C Ref. Temp. (Watts) | Total Losses at 100% Load and 85 °C (Watts) | 200 kV HV BIL Total Losses at 50% Load and 55 °C LL Ref. Temp. and 20 °C NL Ref. Temp. per DOE (Watts) |
|--------|-------------------------------------|-----------------------------------------------------|---------------------------------------------|--------------------------------------------------------------------------------------------------------|
| 750    | 2039                                | 11,027                                              | 13,066                                      | 4800                                                                                                   |
| 1000   | 2595                                | 13,736                                              | 16,331                                      | 6030                                                                                                   |
| 1500   | 3666                                | 18,098                                              | 21,764                                      | 8190                                                                                                   |
| 2000   | 4679                                | 21,049                                              | 25,728                                      | 9940                                                                                                   |
| 2500   | 5636                                | 22,589                                              | 28,225                                      | 11,280                                                                                                 |
| 3000   | 6094                                | 25,028                                              | 31,122                                      | 12,350                                                                                                 |
| 3750   | 7303                                | 28,715                                              | 36,018                                      | 14,480                                                                                                 |
| 5000   | 9300                                | 34,531                                              | 43,831                                      | 17,930                                                                                                 |
| 7500   | 13,222                              | 44,940                                              | 58,162                                      | 24,460                                                                                                 |
| 10,000 | 17,051                              | 53,715                                              | 70,766                                      | 30,480                                                                                                 |

**Note:** Losses offered are typical only, not guaranteed. Losses based on aluminum windings. Losses based on LV rating 2-5 kv.

## Technical Data

**Table 13.0-44. Typical Losses for Dry-Type Transformers (Watts)**

| kVA Rating | VPI/VPE      |           |            | Cast Coil/RESIBLOC |           |            |
|------------|--------------|-----------|------------|--------------------|-----------|------------|
|            | No Load Loss | Load Loss | Total Loss | No Load Loss       | Load Loss | Total Loss |
| 2000       | 5000         | 15,500    | 20,500     | 5400               | 12,000    | 17,400     |
| 2500       | 6300         | 22,500    | 28,800     | 6900               | 14,200    | 21,100     |
| 3000       | 7900         | 24,000    | 31,900     | 8000               | 16,300    | 24,300     |
| 5000       | 10,500       | 26,500    | 37,000     | 12,400             | 18,000    | 30,400     |
| 7500       | 13,200       | 38,000    | 51,200     | 19,200             | 20,000    | 39,200     |
| 10,000     | 15,200       | 47,200    | 62,400     | 21,000             | 28,800    | 49,800     |

**Note:** Losses offered are typical only, not guaranteed. Loss estimates based on aluminum windings for VPI and copper windings for Cast/RESIBLOC. Losses based on LV rating 2–5 kV.