



Tested Top Quality

Location:

Neustadt (Wied), Germany

Segment:

MOEM

Problem:

To achieve a daily production of over one million toothbrushes, a highly reliable technology is absolutely vital.

Solution:

XP700 touch display PLC, MA compact controller with CANopen interface, RMQ pilot devices

Results:

The control of the entire bristle embedding system is handled by Eaton products

Contact Information

Christian Buecker
Trade Press Manager
ChristianBuecker@Eaton.com

We are regarded as highly reliable partners by our customers, and for this our thanks must also go to Zahoransky toothbrush machines and Eaton automation technology

Andreas Walgenbach, M+C Schiffer

Background

Every day we make use of some objects without giving them much thought, and the same goes for how they are manufactured. The production of toothbrushes, for example, requires the use of a very mature technology and a great deal of know-how. M+C Schiffer, based in Neustadt near Cologne, is an internationally recognized innovator in toothbrush production, and produces over one million toothbrushes a day in three shifts, seven days a week, on fully automated manufacturing lines.

Challenges

The production of toothbrushes involves a precisely coordinated chain of different processing stations: M+C Schiffer developed the complete production process themselves and integrates injection molding machines, handling systems as well as processing and packaging machines in the production chain. M+C Schiffer also develops new toothbrush models together with customers, and these include well-known companies and their brand prod-

ucts, such as GlaxoSmithKline with Dr. Best Aquafresh and Sensodyne, Johnson&Johnson with Reach, P&G with OralB and Blend-a-mend, as well as discount stores and drugstores such as Aldi, Rewe, dm, Rossmann and Schlecker.

The time synchronization of the process steps on the one hand, and the speed of individual processes on the other, present a particular challenge in the manufacturing process. Production at M+C Schiffer is fully automated in line, right through to packaging, as only a "no human touch" production meets the hygiene requirements specified.

Multi-component injection molding machines are used in the first production step to produce up to 32 toothbrush base bodies made from polypropylene (PP). The second component made from soft TPE is injected in the second operating cycle. This produces up to 80 toothbrush handles a minute. A handling system then transports the toothbrush base bodies to the bristle embedding plant. The specialist for this segment is Zahoransky, a group



Powering Business Worldwide

Eaton Corporation is a diversified power management company with more than 100 years of experience providing energy-efficient solutions that help our customers effectively manage electrical, hydraulic and mechanical power. With 2011 sales of \$16.0 billion, Eaton is a global technology leader in electrical components, systems and services for power quality, distribution and control; hydraulics components, systems and services for industrial and mobile equipment; aerospace fuel, hydraulics and pneumatic systems for commercial and military use; and truck and automotive drivetrain and powertrain systems for performance, fuel economy and safety. Eaton has approximately 73,000 employees and sells products to customers in more than 150 countries. For more information, visit www.eaton.com.



Enabling user-friendly and intuitive operation: The 15 inch touch display comes with a robust infra-red touch panel with safety glass.



24h operation: Only with a high level of automation for the toothbrush machine is it possible to achieve production volumes in the millions.

of companies based in Todtnau-Geschwend. The bristles, which are also called filaments, are embedded in every individual hole of the toothbrush bodies at a frequency of 1000 cycles a minute. The filament bundles are embedded using an anchor wire (flat type of special wire) which is punched into the recesses of the bristle carrier at high precision with the centrally folded filaments. Depending on the type of toothbrush, up to 50 filament bundles in different lengths, colors and bundle positions are thus embedded in succession. In further production steps, the filaments are cut to defined lengths and rounded in multi-stage grinding processes.

The quality assurance is provided by a fully automated camera-supported control process, which ensures that only fault-free toothbrushes reach the packaging station. Transparent packaging film is given its final shape in the plastic thermoforming process. M+C Schiffer packs products in a range of different package variants in order to meet the

relevant customer requirements. To achieve a daily production of over one million toothbrushes, a highly reliable technology is absolutely vital.

Solution

The control of the entire bristle embedding system is handled by an Eaton compact PLC. The data exchange to the servo controllers, remote I/Os and operator display is implemented via CAN bus. An Eaton XP700 industrial PC with a 15 inch touch display is used for operation and assigning plant parameters. The ruggedly designed infra-red touch display with safety glass ensures a high degree of reliability and meets specified hygiene requirements in accordance with the applicable food regulations. Thanks to its compact housing design and small mounting depth, the touch display can be integrated ergonomically in machines and plants. Local programming access in the field is provided via Eaton RMQ-USB and RJ45 terminals (IP65). The integrated web

server enables the controller to be accessed remotely.

Eaton's Galileo software is used for visualization, and is an easy to learn and yet powerful project design environment. With its non-sector specific concept, Galileo offers seamless project designing for all XP/XV operator units from the Eaton HMI product range as well as for PC runtime solutions. Galileo always provides the project designer with the full functionality without any graduated restrictions on tags (variables) or screens, according to the performance specifications of the panel used.

Users program the Eaton controller with XSoft-CoDeSys-2: This technically mature software based on the CoDeSys standard of 3S is impressive, thanks to its simple handling, and is well established in the automation world.

Results

Dipl.-Ing. Andreas Walgenbach, project manager at M+C Schiffer, sums up as follows: "Our cus-

tomers require just-in-time production for particular product launches or for special marketing campaigns. We then have to produce a specific number of products, often in the millions and deliver exactly on time. We can only keep to these delivery times if we can count on absolutely reliable production technology, components and suppliers. We are regarded as highly reliable partners by our customers, and for this our thanks must also go to Zahoransky toothbrush machines and Eaton automation technology."

Dipl.-Ing. Robert Dous, Director Sales & Marketing at Zahoransky: "Eaton's control and automation technology is an essential component in meeting the demanding requirements of toothbrush production at M+C Schiffer and ensuring highly reliable systems. Only in this way, can we meet our extremely high standard."